


CAT#	A	B	C
1550	.820	1.00	1.12
1551	1.00	1.25	2.50
1552	1.125	1.125	2.8125
1553	1.375	1.375	3.0625
1554	1.75	1.75	3.1875
1555	2.00	2.375	3.50
1556	2.50	2.50	4.50
1557	3.00	3.00	4.875
1558	3.625	3.875	5.375
1559	4.0625	4.5625	5.875
1559A	4.6875	5.0625	6.6875

RIGHT ANGLE CONDUIT SUPPORT

MALLEABLE IRON

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1550	52001	3/8"	-	50	25
1551	52002	1/2"	-	50	40
1552	52003	3/4"	-	50	43
1553	52004	1"	-	50	48
1554	52005	1 1/4"	-	50	53
1555	52006	1 1/2"	-	50	58
1556	52007	2"	-	50	85
1557	52008	2 1/2"	-	25	106
1558	52009	3"	-	25	110
1559	52011	3 1/2"	-	25	128
1559A	52010	4"	-	25	140




CAT#	A	B
1560	2.00	1.370
1561	2.875	1.4375
1562	3.0625	1.6875
1563	3.25	2.00
1564	3.625	2.125
1565	3.875	2.1875
1566	4.625	2.875
1567	5.25	3.25
1568	5.875	3.875
1569	6.3125	4.3125
1570	6.8125	4.8125

PARALLEL CONDUIT SUPPORT

MALLEABLE IRON

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1560	52012	3/8"	-	50	32
1561	52013	1/2"	-	50	58
1562	52014	3/4"	-	50	64
1563	52015	1"	-	50	70
1564	52016	1 1/4"	-	25	72
1565	52017	1 1/2"	-	25	93
1566	52018	2"	-	25	100
1567	52019	2 1/2"	-	25	135
1568	52020	3"	-	10	155
1569	52021	3 1/2"	-	10	190
1570	52022	4"	-	10	205



CAT#	A	B
1571	2.8125	2.125
1572	2.9375	2.375
1573	3.0625	2.625
1574	3.0625	3.0625
1575	3.9375	3.25
1576	4.50	4.0625
1577	5.125	4.625
1578	5.75	5.25

EDGE TYPE CONDUIT SUPPORT

MALLEABLE IRON

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1571	52023	1/2"	-	50	67
1572	52024	3/4"	-	50	71
1573	52025	1"	-	25	85
1574	52066	1 1/4"	-	25	91
1575	52027	1 1/2"	-	25	115
1576	52028	2"	-	25	135
1577	52029	2 1/2"	-	10	183
1578	52030	3"	-	10	230

