



Southwire™

DCP8 / DCPA8 / DCP8D / DCPA8D

Diagonal Cutting Pliers

THE HIGH LEVERAGE DESIGN OF THESE DIAGONAL CUTTING PLIERS PROVIDES GREATER CUTTING POWER WHILE THE HOT RIVETED JOINT ENSURES SMOOTH ACTION WITH NO HANDLE WOBBLE.

SUPERIOR CUTTING POWER

induction hardened cutting blades ensure efficient and last cutting surfaces. Effectively cuts most hardened wire, ACSR, and small bolts

DURABLE

drop forged CRV steel for durability

SMOOTH ACTION

hot riveted pivot joint for smooth action and no wobble. High leverage design provides maximum cutting power

COMFORTABLE GRIPS

available in dual molded comfort grips and plastic dipped handles



Southwire™

Tools & Assembled Products Division

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-SWT00LS
(855-798-6657)



Scan code to see more
Southwiretools.com



Southwire™

DCP8 / DCPA8 / DCP8D / DCPA8D

Diagonal Cutting Pliers



DCP8

- COMFORT GRIP



DCPA8

- COMFORT GRIP
- ANGLED HEAD



DCP8D

- DIPPED GRIP



DCPA8D

- DIPPED GRIP
- ANGLED HEAD

MODEL #	STOCK #	DESCRIPTION:	HEIGHT:	WIDTH:	DEPTH:	WEIGHT:	HEAD TYPE	HANDLE COLOR	HANDLE FINISH
DCP8D	582894	8" HI LEV DIAG CUT PLIERS HEAD DIP HANDLE	8"	2"	0.63"	9.8 oz	STANDARD	YELLOW	DIPPED GRIP
DCPA8D	582895	8" HI LEV DIAG CUT PLIER ANGLE HEAD DIP HANDLE	8"	2"	0.63"	9.8 oz	ANGLED	YELLOW	DIPPED GRIP
DCP8	589933	8" HI LEV DIAGONAL PLIERS	8.25"	2.25"	0.75"	11.6 oz	STANDARD	YELLOW/BLK	COMFORT GRIP
DCPA8	589932	8" HI LEV DIAGONAL PLIERS ANGLE HEAD	8.25"	2.25"	0.75"	11.6 oz	ANGLED	YELLOW/BLK	COMFORT GRIP



Southwire™

Tools & Assembled Products Division

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

1-855-SWT00LS
(855-798-6657)



Scan code to see more
Southwiretools.com