



Southwire™

LNP6 / LNP6D / LNP7 / LNP8S / LNP8SD

# Long Nose Pliers

**SOUTHWIRE™ LONG NOSE PLIERS PROVIDE A BETTER GRIP WITHOUT SACRIFICING TOOL STRENGTH OR DURABILITY.**

**LONG NOSE**

Long nose design for forming and looping wire and handling small parts

**SUPERIOR CUTTING POWER**

Precision induction-hardened cutting knives

**UTILITY DESIGN**

Knurled jaws for sure wrapping and looping

**SMOOTH ACTION**

High leverage, hot rivet design for smooth action and no handle wobble

**SOLID CONSTRUCTION**

Drop forged CRV Steel for durability



Southwire™

Tools & Assembled Products Division

BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™

**1-855-SWTOOLS**  
**(855-798-6657)**



Scan code to see more  
[Southwiretools.com](http://Southwiretools.com)



Southwire™

LNP6 / LNP6D / LNP7 / LNP8S / LNP8SD

# Long Nose Pliers



**LNP6**

- COMFORT GRIP
- 6 INCH



**LNP6D**

- DIPPED GRIP
- 6 INCH



**LNP7**

- COMFORT GRIP
- 7 INCH



**LNP8S**

- COMFORT GRIP
- STRIPPING
- 8 INCH



**LNP8SD**

- DIPPED GRIP
- STRIPPING
- 8 INCH

MODEL #	STOCK #	DESCRIPTION:	HEIGHT:	WIDTH:	DEPTH:	WEIGHT:	HANDLE COLOR	HANDLE FINISH	ADDITIONAL FEATURES
LNP6D	582898	6" LONG NOSE PLIERS W/SIDE CUT DIP HANDLE	6.88"	2.25"	0.56"	5 oz	BLUE	DIPPED GRIP	SIDE CUTTER
LNP8SD	589930	8" HVY DTY LONG NOSE PLIER SUT STRIP DIP HANDLE	8.38"	2.13"	0.63"	10.3 oz	BLUE	DIPPED GRIP	SIDE CUTTER & WIRE STRIPPER
LNP6	589926	6" LONG NOSE PLIERS W/SIDE CUTTER	7"	2.25"	0.75"	5.5 oz	BLUE/BLK	COMFORT GRIP	SIDE CUTTER
LNP7	589927	7" LONG NOSE PLIERS W/SIDE CUTTER	7.13"	2.25"	0.75"	5.7 oz	BLUE/BLK	COMFORT GRIP	SIDE CUTTER
LNP8S	589928	8" HVY DTY LONG NOSE PLIER SUT STRIP	8.5"	2.13"	0.88"	10.3 oz	BLUE/BLK	COMFORT GRIP	SIDE CUTTER & WIRE STRIPPER



Southwire™

Tools & Assembled Products Division

[BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.]

**1-855-SWT00LS**  
**(855-798-6657)**



Scan code to see more  
[Southwiretools.com](http://Southwiretools.com)