

WIRING DIAGRAMS		LOCKNUT LN-M18		SPECIFICATIONS																																																																												
<p>OUTPUT: RZ3X</p>				<table border="1"> <tr><td>OPERATING VOLTAGE</td><td>20-250 VAC</td></tr> <tr><td>LINE FREQUENCY</td><td>40-60 Hz</td></tr> <tr><td>DIFFERENTIAL TRAVEL (HYSTERESIS)</td><td>3-15% (<5% TYPICAL)</td></tr> <tr><td>VOLTAGE DROP ACROSS CONDUCTING SENSOR</td><td>≤7.0 V at 500 mA</td></tr> <tr><td>OUTPUT FUNCTION -RZ</td><td>NORMALLY CLOSED 2-WIRE AC SELF-CONTAINED</td></tr> <tr><td>SHORT-CIRCUIT PROTECTED</td><td>NO</td></tr> <tr><td>CONTINUOUS LOAD CURRENT</td><td>≤500 mA</td></tr> <tr><td>OFF-STATE (LEAKAGE) CURRENT</td><td>≤1.7 mA</td></tr> <tr><td>MINIMUM LOAD CURRENT</td><td>≥5.0 mA</td></tr> <tr><td>INRUSH CURRENT</td><td>≤8.0 A (≤10 ms/5 Hz)</td></tr> <tr><td>TIME DELAY BEFORE AVAILABILITY</td><td>≤25 ms</td></tr> <tr><td>POWER-ON EFFECT PROTECTION</td><td>INCORPORATED</td></tr> <tr><td>PROTECTION AGAINST TRANSIENTS</td><td>5 kV, 10 ms, 10 kΩ</td></tr> <tr><td>OPERATING TEMPERATURE</td><td>-25°C to +70°C (-13°F to +158°F)</td></tr> <tr><td>ENCLOSURE</td><td>MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67</td></tr> <tr><td>SHOCK</td><td>30 g, 11 ms</td></tr> <tr><td>VIBRATION</td><td>55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)</td></tr> <tr><td>LED FUNCTION</td><td>RED: OUTPUT ENERGIZED</td></tr> <tr><td>SENSING RANGE</td><td>5 mm = .197" (NOMINAL)</td></tr> <tr><td>SWITCHING FREQUENCY</td><td>20 Hz</td></tr> <tr><td>REPEATABILITY</td><td>≤2% of RATED OPERATING DISTANCE</td></tr> <tr><td>EMBEDDABLE (SHIELDED)</td><td>YES</td></tr> <tr><td>MATING PLUGS/CABLES</td><td>3-PIN "MINIFAST" CONSTRUCTION</td></tr> </table>		OPERATING VOLTAGE	20-250 VAC	LINE FREQUENCY	40-60 Hz	DIFFERENTIAL TRAVEL (HYSTERESIS)	3-15% (<5% TYPICAL)	VOLTAGE DROP ACROSS CONDUCTING SENSOR	≤7.0 V at 500 mA	OUTPUT FUNCTION -RZ	NORMALLY CLOSED 2-WIRE AC SELF-CONTAINED	SHORT-CIRCUIT PROTECTED	NO	CONTINUOUS LOAD CURRENT	≤500 mA	OFF-STATE (LEAKAGE) CURRENT	≤1.7 mA	MINIMUM LOAD CURRENT	≥5.0 mA	INRUSH CURRENT	≤8.0 A (≤10 ms/5 Hz)	TIME DELAY BEFORE AVAILABILITY	≤25 ms	POWER-ON EFFECT PROTECTION	INCORPORATED	PROTECTION AGAINST TRANSIENTS	5 kV, 10 ms, 10 kΩ	OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)	ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67	SHOCK	30 g, 11 ms	VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)	LED FUNCTION	RED: OUTPUT ENERGIZED	SENSING RANGE	5 mm = .197" (NOMINAL)	SWITCHING FREQUENCY	20 Hz	REPEATABILITY	≤2% of RATED OPERATING DISTANCE	EMBEDDABLE (SHIELDED)	YES	MATING PLUGS/CABLES	3-PIN "MINIFAST" CONSTRUCTION																													
OPERATING VOLTAGE	20-250 VAC																																																																															
LINE FREQUENCY	40-60 Hz																																																																															
DIFFERENTIAL TRAVEL (HYSTERESIS)	3-15% (<5% TYPICAL)																																																																															
VOLTAGE DROP ACROSS CONDUCTING SENSOR	≤7.0 V at 500 mA																																																																															
OUTPUT FUNCTION -RZ	NORMALLY CLOSED 2-WIRE AC SELF-CONTAINED																																																																															
SHORT-CIRCUIT PROTECTED	NO																																																																															
CONTINUOUS LOAD CURRENT	≤500 mA																																																																															
OFF-STATE (LEAKAGE) CURRENT	≤1.7 mA																																																																															
MINIMUM LOAD CURRENT	≥5.0 mA																																																																															
INRUSH CURRENT	≤8.0 A (≤10 ms/5 Hz)																																																																															
TIME DELAY BEFORE AVAILABILITY	≤25 ms																																																																															
POWER-ON EFFECT PROTECTION	INCORPORATED																																																																															
PROTECTION AGAINST TRANSIENTS	5 kV, 10 ms, 10 kΩ																																																																															
OPERATING TEMPERATURE	-25°C to +70°C (-13°F to +158°F)																																																																															
ENCLOSURE	MEETS NEMA 1, 3, 4, 6, 13 AND IEC IP67																																																																															
SHOCK	30 g, 11 ms																																																																															
VIBRATION	55 Hz, 1 mm AMPLITUDE (IN ALL 3 PLANES)																																																																															
LED FUNCTION	RED: OUTPUT ENERGIZED																																																																															
SENSING RANGE	5 mm = .197" (NOMINAL)																																																																															
SWITCHING FREQUENCY	20 Hz																																																																															
REPEATABILITY	≤2% of RATED OPERATING DISTANCE																																																																															
EMBEDDABLE (SHIELDED)	YES																																																																															
MATING PLUGS/CABLES	3-PIN "MINIFAST" CONSTRUCTION																																																																															
				<table border="1"> <tr> <td>MATERIAL</td> <td colspan="2">3RD ANGLE PROJECTION</td> <td colspan="2" rowspan="2"> </td> <td rowspan="2"> TURCK INC 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224 </td> </tr> <tr> <td>FINISH</td> <td colspan="2">BRASS BARREL</td> </tr> <tr> <td>DRWN</td> <td>GMB</td> <td>DATE</td> <td>9/27/88</td> <td colspan="2">PART NO.</td> </tr> <tr> <td>CHKD</td> <td></td> <td>DATE</td> <td></td> <td colspan="2">B15-G18-RZ3X-B1331</td> </tr> <tr> <td colspan="3">DIMENSIONS ARE IN</td> <td>INCHES</td> <td>SIZE</td> <td>REV</td> </tr> <tr> <td colspan="3"></td> <td>mm</td> <td>B</td> <td>B</td> </tr> <tr> <td colspan="3"></td> <td></td> <td>ID NO.</td> <td></td> </tr> <tr> <td colspan="3"></td> <td></td> <td>4373100</td> <td></td> </tr> <tr> <td colspan="3"></td> <td></td> <td>SCALE</td> <td>OF</td> </tr> <tr> <td colspan="3"></td> <td></td> <td>NONE</td> <td></td> </tr> <tr> <td colspan="3"></td> <td></td> <td>BMQD-A\4373100</td> <td></td> </tr> <tr> <td colspan="3"></td> <td></td> <td>SHEET</td> <td></td> </tr> <tr> <td colspan="3"></td> <td></td> <td>OF</td> <td></td> </tr> </table>		MATERIAL	3RD ANGLE PROJECTION				TURCK INC 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224	FINISH	BRASS BARREL		DRWN	GMB	DATE	9/27/88	PART NO.		CHKD		DATE		B15-G18-RZ3X-B1331		DIMENSIONS ARE IN			INCHES	SIZE	REV				mm	B	B					ID NO.						4373100						SCALE	OF					NONE						BMQD-A\4373100						SHEET						OF	
MATERIAL	3RD ANGLE PROJECTION				TURCK INC 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 PHONE: (612) 553-9224																																																																											
FINISH	BRASS BARREL																																																																															
DRWN	GMB	DATE	9/27/88	PART NO.																																																																												
CHKD		DATE		B15-G18-RZ3X-B1331																																																																												
DIMENSIONS ARE IN			INCHES	SIZE	REV																																																																											
			mm	B	B																																																																											
				ID NO.																																																																												
				4373100																																																																												
				SCALE	OF																																																																											
				NONE																																																																												
				BMQD-A\4373100																																																																												
				SHEET																																																																												
				OF																																																																												
<p>WARNING: NO SHORT-CIRCUIT PROTECTION ALWAYS WIRE A LOAD IN SERIES WITH THE SENSOR.</p>																																																																																
<p>REVISIONS</p>																																																																																
B	SEE REVISION DOCUMENT G18-AZ2	GMB	6/12/91																																																																													
REV	DESCRIPTION	DRFT	DATE	CHKD																																																																												