




SPECIFICATIONS	
CONTACT CARRIER MATERIAL	NYLON or PUR
MOLDED HEAD MATERIAL/COLOR	THERMOPLASTIC PUR/YELLOW
CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
COUPLING NUT MATERIAL/PLATING	NICKEL-PLATED BRASS
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
OUTER CABLE JACKET MATERIAL/COLOR	OIL RESISTANT PVC/GREY
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	3x2D AWG
TEMPERATURE RANGE	-40°C to +105°C [-40°F to +221°F]
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68
SPACINGS	to VDE D110 Group C



CABLE LENGTH	TOLERANCE
+ 4% (OR 50mm) OF LENGTH	
- 0% (OR 0mm) OF LENGTH	
WHICHEVER IS GREATER	
STRIP LENGTH	TOLERANCE
0-30mm	±0.50mm
30-40mm	±1.00mm
40-50mm	±1.50mm
50-60mm	±2.00mm
60-80mm	±3.00mm
80-100mm	±4.00mm
OVER 100mm	±5.00mm

NOTES:

1. "4" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

REV	DESCRIPTION	DATE	BY	DATE	EDD NO.
G	UPDATE COUPLING NUTS	12/09/02	JJB	0582	

RELATED DOCUMENTS	3RD ANGLE PROJECTION	TURCK DRAWING & PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	DATE	DESCRIPTION
1. GENERAL		DATE: 07/20/00	DATE: 07/20/00	DESCRIPTION: RIK 4T-6-RS 4T
2. SEE SPECIFICATIONS		SCALE: 1=1.0		
3. FRISH		UNIT OF MEASUREMENT: MILLIMETER [INCH]		
4. SEE SPECIFICATIONS		00 NOT SCALE THIS DRAWING		

TURCK INC	
High Technology Sensors and Automation Control	
IDENTIFICATION NO.	REP: C
FILE: EURO-C/777000636	