



MALE END VIEW



- 1 = BARE (SHIELD)
- 2 = RED (+ VOLTAGE)
- 3 = BLACK (- VOLTAGE)
- 4 = WHITE (CAN_H)
- 5 = BLUE (CAN_L)



FEMALE END VIEW




- 1 = BARE (SHIELD)
- 2 = RED (+ VOLTAGE)
- 3 = BLACK (- VOLTAGE)
- 4 = WHITE (CAN_H)
- 5 = BLUE (CAN_L)



SPECIFICATIONS

CONTACT CARRIER MATERIAL/COLOR	THERMOPLASTIC PUR/GREY
MOLDED HEAD MATERIAL/COLOR	THERMOPLASTIC PUR/GREY
CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
COUPLING NUT MATERIAL/PLATING	NICKEL-PLATED BRASS
RATED CURRENT [A]	9.0 A
RATED VOLTAGE [V]	300 V
OUTER JACKET MATERIAL/COLOR	OIL AND ABRASION RESISTANT PVC/GREY
CONDUCTOR INSULATION MATERIAL	POLYETHYLENE
# OF CONDUCTORS [AWG]	2X15 AWG, 2X18 AWG, 18 AWG DRAIN
TEMPERATURE RATING	-40° to 70°C (-40° to 158°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6,13 AND IEC IP67
SPACINGS	TO VDE 0110 GROUP C



* METERS
SEE NOTES 1 AND 2

SOURCE DRAWING - FOR REFERENCE ONLY

CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

NOTES:

1. IDENTIFICATION NUMBER SHOWN REFERS TO 1 METER LENGTH. OTHER LENGTHS AVAILABLE BY REQUEST.
2. (*) DESIGNATES LENGTH IN METERS.

A	DRAWING RELEASE	RDS	03/20/02	ECO NO.
REV	DESCRIPTION	BY	DATE	

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DOCUMENT IS PROPERTY OF InterlinkBT LLC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-888-546-5880 (763) 694-2300 (763) 694-2399 fax InterlinkBT.com	
MATERIAL		TOLERANCES UNLESS OTHERWISE SPECIFIED		DRAFT		DATE 03/20/02	
SEE SPECIFICATIONS		.X ±0.02 .XX ±0.01 .XXX ±0.005		RDS		SCALE 1=1	
FINISH		ALL MILLIMETER DIMENSIONS ARE REFERENCE ONLY		UNIT OF MEASUREMENT		IDENTIFICATION NO.	
SEE SPECIFICATIONS				INCH [MILLIMETER]		RSM RKM 579-*M (2) U5450-52 (1)	
		DO NOT SCALE THIS DRAWING				FILE: MINI-C\U5450-52	
						REV A	
						SHEET 1 OF 1	