

3M™ Scotchcast™ Flame-Retardant Compound 2131

Data Sheet

March 2011

Description

3M™ Scotchcast™ Flame-Retardant Compound 2131 is a two-part polyurethane resin designed to replace the cable jacket when splicing or repairing mine and portable cables. Its unique formulation makes it particularly suited to withstand the rugged conditions under which mine and portable cables must operate.

Flame-Retardant Compound 2131 is also used as the insulating material for cable splices operating at up to 1000 volts and designed for 194°F (90°C) continuous use/266°F (130°C) overload.

When used in accordance with the appropriate kit configuration, Compound 2131 meets Part 7, Title 30 CFR and carries the following MSHA approvals:

07-KA060002-MSHA	3M™ Scotchcast™ Inline Splice Kit for Flexible Cable 82-F Series 3M™ Scotchcast™ Flexible Power Cable Tap Splice 82-BF1
07-KA060007-MSHA	3M™ Scotchcast™ Mine and Portable Splice Kits 8096 Series 3M™ Three-Conductor Inline Splicing Kits 5750 and 5760 Series 3M™ Scotchcast™ Jacket Repair Kits M Series*

* The Compound 2131 is not included with the "M" Series kits and must be ordered separately.

This compound is available in a convenient, pre-measured, two-part closed mixing pouch of the following sizes:

Bag	Weight oz (g)	Volume in ³ (cm ³)
B Size	7.5 (213)	10.6 (175)
C Size	21.5 (612)	30.6 (502)

Bulk components of Compound 2131 are also available separately in 5 gallon (18,9 L) containers:

- Each container of Part A contains 44.5 pounds (20,1 kg) [635 fl.oz. (18,7 L)]
- Each container of Part B contains 46.5 pounds (21,0 kg) [566 fl.oz. (16,7 L)]

Features

- Flame-retardant
- Bonds to most modern cable jackets
- Bonds to itself
- Tough, yet flexible
- Available in unique closed mixing pouch for easy mixing and pouring
- Excellent multi-purpose moisture sealing resin

Applications

- To replace or repair the jacket on both single and multi-core power cables
- To insulate between conductors of multi-core splices operating at up to 1000 volts
- To seal the crotch or sheath when terminating multi-core cables

3M™ Scotchcast™ Flame-Retardant Compound 2131

Typical Properties Not for specifications. Values are typical, not to be considered minimum or maximum. Properties measured at room temperature 73°F (23°C) unless otherwise stated.

Physical Properties (Test Method)	Typical Value US units (metric)
Color	Black
Hardness (ASTM D2240)	82 Shore A
Density	0.703 oz/in ³ (1,217 g/cm ³)
Tensile Strength (ASTM D412)	1038 psi (73,0 kg/cm ²)
Elongation (ASTM D412)	339%
Glass Transition Temperature, T_g (DMA)	-112 °F (-80°C)
Maximum Exotherm, 100g (3M Method TM-67)	146°F (63,5°C) rise
Gel Time @ 75°F (23°C) (3M Method TM-67)	17 minutes
Moisture Absorption (ASTM D471) 168 hrs. Immersion @ 212°F (100°C)	4.9%

Electrical Properties (Test Method)	Typical Value
Dielectric Strength (ASTM D149)	343 V/mil (13,5 kV/mm)
Dielectric Constant, @ 60Hz (ASTM D150)	5.22 @ 73°F (23°C) 6.33 @ 140°F (60°C) 6.56 @ 194°F (90°C)
Dissipation Factor, @ 60Hz (ASTM D150)	5.6% @ 73°F (23°C) 7.9% @ 140°F (60°C) 17.0% @ 194°F (90°C)

Usage Information **IMPORTANT:** Product should remain in the sealed container/envelope until ready to use. In cold weather, warm closed mixing pouch to 60°F (16°C) or warmer before mixing. Keep in a warm area, such as truck cab or inside pocket, until ready to use.

Closed Mixing Pouch:

- Tear open the protective envelope and remove the closed mixing pouch
- Before breaking the barrier, squeeze the bag to premix the separate components.
- Firmly grasp each flat side of the bag near the center barrier, while pulling the sides of the barrier apart and rolling the sides of thumbs through the barrier. Break the barrier all the way across to the side seals.
- Alternately squeeze each end of the bag, forcing the resin back and forth (30 seconds).
- Strip the resin from the corners of the bag and continue to mix until the color is uniform (additional 30 seconds, maximum).
- Clip off a corner of the closed mixing pouch and pour

Bulk Components:

Measure the appropriate quantity of each component as indicated in the table below, then thoroughly mix to a uniform color and consistency prior to use. Bulk components should be blanketed with nitrogen to prevent moisture contamination.

Component	Color	Weight Ratio (w/w)	Volume Ratio (v/v)
Part A	Pale Yellow	1	1
Part B	Black	2.1	1.79

3M™ Scotchcast™ Flame-Retardant Compound 2131

Usage Information, Typical De-Mold/Cure Time: *continued*

Temperature	De-Mold Time	Approximate Cure Time
70°F (21°C)	1.5 – 2 hrs	16 – 24 hours
50°F (10°C)	3.5 – 4 hrs	24 – 30 hours
32°F (0°C)	6 – 8 hrs	36+ hours

NOTE: Values are typical, not to be considered minimum or maximum. Always confirm that material is no longer tacky prior to de-molding.

Caution

Working around energized electrical systems may cause serious injury or death. Installation should be performed by personnel familiar with good safety practice in handling electrical equipment. De-energize and ground all electrical systems before installing product.

Handling and Safety Precautions:

Read all Health Hazard, Precautionary and First Aid statements found in the Material Safety Data Sheet (MSDS) and/or product label of chemicals prior to handling or use.

Shelf Life & Storage

3M™ Scotchcast™ Flame-Retardant Compound 2131 has a 3-year shelf life from date of manufacture when stored in the factory-sealed packaging under humidity controlled storage (10°C/50°F to 27°C/80°F and <75% relative humidity).

Availability

Please contact your local distributor; available from 3M.com/electrical [Where to Buy] or call 1.800.245.3573.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product, which are not contained in 3M's current publications, or any contrary statements contained on your purchase order, shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability

This product will be free from defects in material and manufacture at the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

3M and Scotchcast are trademarks of 3M Company.



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800.245.3573
Fax 800.245.0329
www.3M.com/electrical

Please recycle
© 3M 2011 All rights reserved
78-8129-9502-1 B