

# S10



Socket for C10-C14-CSS relays  
DIN rail or panel mountable


10 A 250 V

Interface I/O socket, with terminals in-line  
for relays C10A, C10G, C10T, CSS




### Specifications

Poles	1
Nominal load	10 A/250 V
Dielectric strength	
Coil - contacts	5 KV
Terminals - Rail	5 KV
Max. screw torque	1.2 Nm
Multi-core capacity	22-14 AWG
Solid wire capacity	4 mm <sup>2</sup> or 2 x 2.25 mm <sup>2</sup>
Weight average	28 g

### Wiring Diagram



### Dimensions - mm



Bridge Bus Bar S10-BB

### Other Aspects

- Hard brass tin-plated terminals
- Brass zinc-plated solid screws
- Integrated clip
- Removable marking label

### Accessories

- Bridge bar for coil and movable contact (S10-BB)
- Integrated clip
- DIN rail or panel mounting
- Maximum current through bridge 10 A
- Maximum current input common cable 20 A

