

Inductive Sensors



Housing Style	Part Number	ID Number	Features	Sensing Range (mm)	Output
12 mm - Non-Embeddable, Potted-In Cable 	Ni 4-M12-AD4X	T4405200		4	2-Wire DC
	Ni 8-M12-AD4X	T4411235	<i>Extended Range</i>	8	
	Ni 8-M12-AD4X/S90	T4411235-1	<i>Extended Range</i>	8	
	Ni 4-M12-AN6X	T4606380		4	3-Wire DC NPN
	Ni 8-M12-AN6X	T4611318	<i>Extended Range</i>	8	
	Ni 8U-EM12-AN6X	M1644320	<i>Ext. Range, Uprox</i>	8	
	Ni 8U-M12-AN6X	M1644120	<i>Ext. Range, Uprox</i>	8	
	Ni 4-M12-AP6X	T4605200		4	3-Wire DC PNP
	Ni 4-M12-AP6X/S100	M4605201	<i>High Temp. 100°C</i>	4	
	Ni 8-M12-AP6X	T4611319	<i>Extended Range</i>	8	
	Ni 8U-EM12-AP6X	M1644300	<i>Uprox</i>	8	
	Ni 8U-M12-AP6X	M1644100	<i>Uprox</i>	8	
	Ni 4-M12-VN6X	T1640400	<i>Ext. Range, Comp. Output</i>	4	4-Wire DC NPN
	Ni 8-M12-VN6X	T4611321	<i>Ext. Range, Comp. Output</i>	8	
	Ni 4-M12-VP6X	T1630400	<i>Ext. Range</i>	4	4-Wire DC PNP
	Ni 8-M12-VP6X	T4611322	<i>Ext. Range, Comp. Output</i>	8	

For detailed sensor specifications see Section M.
Normally Closed versions available upon request, consult factory.

Courtesy of Steven Engineering, Inc.-230 Ryan Way, South San Francisco, CA 94080-6370-Main Office: (650) 588-9200-Outside Local Area: (800) 258-9200-www.stevenengineering.com

D73 B1007

www.turck.us

1-800-544-7769

Fax: (763) 553-0708

TURCK Inc. Minneapolis, MN 55441



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Face	End Cap	Power LED	Output LED	Cable Length/ Cable Mat.	Wiring Diagram #	Wiring Diagrams
10-65 VDC	1000	≤100	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	1	Diagram 1
	1000	≤100	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	1	
	1000	≤100	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PUR	1	
10-30 VDC	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	2	Diagram 2
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	2	
	2000	≤200	-30 to +85	IP 68	SS	PA 12	EPTR	N/A	YE	2M/PVC	2	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	2	
10-30 VDC	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	3	Diagram 3
	2000	≤200	-25 to +100	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	3	
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	3	
	2000	≤200	-30 to +85	IP 68	SS	PA 12	EPTR	N/A	YE	2M/PVC	3	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	3	
10-30 VDC	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	4	Diagram 4
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	4	
10-30 VDC	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	5	Diagram 5
	2000	≤200	-25 to +70	IP 67	CPB	PA 12	EPTR	N/A	YE	2M/PVC	5	

Barrels

For material descriptions see page M36.