

Three level sensor terminal blocks without ground connection

Compression clamp


 DIN 3

End stop	th. 9,1 mm	BAMH	0114 836.00
<i>Other end stops : See Accessories section</i>			
Rail	35 x 7,5 x 1	PR30 prepunched	0173 220.05
Rail	35 x 15 x 2,3	PR4	0168 500.12
Rail	35 x 15 x 1,5	PR5 prepunched	0101 598.26
<i>Other rails : See Accessories section</i>			
<i>Other accessories : See Accessories section</i>			

Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.

Accessories



1 End section	grey
2 Assembled jumper bar	22 A
jumper bar (without IP20 protection)	22 A
3 Connector plate	22 A
4 IDC jumper	24 A




R See section on markers marking method

D 2,5/6.D

Spacing 6 mm +0,05 (.238")

81 3.19"




center of rail 36,5 1.44"


Three level block for sensor


D 2,5/6.DL

Spacing 6 mm +0,05 (.238")



Three level block for sensor with LED indication between middle and upper level (red 24V=)

Color	Type	Part numbers
Grey	 D 2,5/6.D	0115 542.12

Color	Type	Part numbers
Grey	 D 2,5/6.DL	0115 537.05

Characteristics				
Wire size				
	NFC	DIN	UL	CSA
Compression Solid wire	0,2-2,5 mm ²	24-12 AWG	24-12 AWG	
clamp Stranded wire	0,22-2,5 mm ²	24-12 AWG	24-12 AWG	

Characteristics				
Wire size				
	NFC	DIN	UL	CSA
Compression Solid wire	0,2-2,5 mm ²	20-12 AWG	22-14 AWG	
clamp Stranded wire	0,22-2,5 mm ²	20-12 AWG	22-14 AWG	

Voltage			
Rated	380 V Gr.C	300 V	300 V
Pulse			
Pollution degree			

Current			
Rated	22 A	20 A	20 A

Wire size			
Rated / Gauge	2,5 mm ²	12 AWG	12 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
6 mm	3,5 mm	0,4-0,6 Nm	IP20
.24"	.138"	3.5-5.3 lb.in	NEMA 1



Voltage			
Rated	380 V Gr.C	300 V (1)	300 V (1)
Pulse			
Pollution degree			

Current			
Rated	22 A	20 A	20 A

Wire size			
Rated / Gauge	2,5 mm ²	12 AWG	14 AWG
Wire stripping length	Recomm. Screwdriver	Recomm. torque	Protection
6 mm	3,5 mm	0,4-0,6 Nm	IP20
.24"	.138"	3.5-5.3 lb.in	NEMA 1

Type	Part numbers
FED3E th. 3,0 mm	0116 771.20
BJD6 2 poles	0178 024.25
BJD6 3 poles	0178 025.26
BJD6 4 poles	0178 026.27
BJD6 5 poles	0178 027.20
BJD6 10 poles	0178 032.25
BJD6 20 poles	0178 033.26
EL61	0177 812.17
AD2,5	0114 205.20

Type	Part numbers
FED3E th. 3,0 mm	0116 771.20
BJD6 2 poles	0178 024.25
BJD6 3 poles	0178 025.26
BJD6 4 poles	0178 026.27
BJD6 5 poles	0178 027.20
BJD6 10 poles	0178 032.25
BJD6 20 poles	0178 033.26
EL61	0177 812.17
AD2,5	0114 205.20



⑤ RC65 red - blank	0103 776.01
RC65 blue - blank	0103 775.00

⑤ RC65 red - blank	0103 776.01
RC65 blue - blank	0103 775.00

Note : (1) 24 VDC on LED circuit.