

## General Information

<b>Extended Product Type:</b>	RC810
<b>Product ID:</b>	1SNA234000R0200
<b>EAN:</b>	3472592340005
<b>Catalog Description:</b>	RC810 Terminal Block Markers - Blank card - White - Polyamid

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C
<b>Color:</b>	White
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	39269097
<b>Data Sheet, Technical Information:</b>	1SNC160023C0201
<b>Declaration of Conformity - CE:</b>	1SND225156C1000
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>EAN:</b>	3472592340005
<b>ETIM 4:</b>	EC000761 - Labelling for terminal block
<b>ETIM 5:</b>	EC000761 - Labelling for terminal block
<b>ETIM 6:</b>	EC000761 - Labelling for terminal block
<b>Environmental Information:</b>	1SND220060E1000
<b>Flammability According to UL94:</b>	V2
<b>Function:</b>	Blank card
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Instructions and Manuals:</b>	1SNC160023C0201
<b>Insulation Material:</b>	Polyamide
<b>Invoice Description:</b>	RC810 Terminal Block Markers - Blank card - White - Polyamid
<b>Minimum Order Quantity:</b>	10 piece
<b>Order Multiple:</b>	10 piece
<b>Package Level 1 EAN:</b>	3472592340005
<b>Package Level 1 Gross Weight:</b>	0.082 kg
<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 2 Units:</b>	1155 piece
<b>Product Main Type:</b>	RC810
<b>Product Name:</b>	Marker
<b>Product Net Depth:</b>	110.5 mm
<b>Product Net Height:</b>	89.4 mm
<b>Product Net Length:</b>	8 mm
<b>Product Net Weight:</b>	8.2 g
<b>Product Net Width:</b>	2.1 mm
<b>RoHS Date:</b>	20140203
<b>RoHS Information:</b>	1SND230010F0204
<b>RoHS Status:</b>	Following EU Directive 2011/65/EC
<b>Selling Unit of Measure:</b>	piece
<b>Suitable For:</b>	BAM4 C6/8

C6/8.P  
C6/8.ST4  
CPF  
D1.5/8.SF.ADO  
D1.5/8.SNN.ADO  
D10/10.1.2L  
D10/10.1.P.2L  
D10/10.3L  
D10/10.P.3L  
D120/42.AF  
D120/42.FF  
D120/42.FF.Ex  
D150/31.D10  
D16/12.2L  
D16/12.3L  
D16/12.P.2L  
D16/12.P.3L  
D185/55.AF  
D185/55.FF  
D185/55.FF.Ex  
D2.5/8.ADO  
D2.5/8.ADO.NF  
D2.5/8.P.ADO  
D2.5/8.S.ADO  
D2.5/8.S.ADO.NF  
D2.5/8.SF.ADO2  
D2.5/8.SNNT.ADO2  
D2.5/8.SNT2.ADO  
D240/36.D10  
D300/55.FF  
D300/55.FF.Ex  
D35/16.2L  
D35/16.P.2L  
D35/27.AF  
D35/27.FF  
D35/27.FF.Ex  
D4/8.ADO  
D4/8.ADO.NF  
D4/8.D2.P.SF  
D4/8.P.ADO  
D4/8.S.2A.ADO2  
D4/8.S.ADO  
D4/8.SF.I.ADO  
D4/8.SN.ADO  
D4/8.SN.I.ADO  
D6/8.2L  
D6/8.3L  
D6/8.ADO  
D6/8.ADO.RS  
D6/8.D2.ADO  
D6/8.NT.L  
D6/8.P  
D6/8.P.2L  
D6/8.P.3L  
D6/8.P.ADO  
D6/8.ST.RS  
D70/32.AF  
D70/32.FF  
D70/32.FF.Ex  
DR4/8SF  
E6/8  
ES8-CG  
HD6/8  
HD6/9  
M10/10.P  
M10/10

M16/12  
M16/12.2A.G  
M16/12.P  
M35/16  
M35/16.2A.2G  
M35/16.P  
M4/8  
M4/8.D2.SF  
M4/8.D2.SF.NC  
M4/8.SF  
M4/8.SF.NC  
M4/8.SN  
M6/8  
M6/8.D  
M6/8.D2.NC  
M6/8.NC  
M6/8.NT  
M6/8.RS  
M6/8.S  
M6/8.SB  
M6/8.SNB  
M6/8.ST  
M6/8.STP  
M6/8.STP.RS  
ML10/13.SF  
ML10/13.SN  
MS6/8

