



Feed through and ground terminal blocks

Screw clamp, 3 3 3 DIN 1-3

Terminal blocks



M 6/8 - 6 mm² blocks - 8 mm .315" spacing

Characteristics

Wire size mm ² / AWG	Solid Stranded	IEC NFC	DIN	UL	CSA
		0.5 - 10		22-8 AWG	24-8 AWG
		0.5 - 6			
Voltage	V	800	600	600	
Current	A	41	50	55	
Short circuit current (M 6/8.PI)	A / s	720A/1s			
Rated wire size	mm ² / AWG	6 mm ²	8 AWG	8 AWG	
Wire stripping length	mm / inches	12 mm / .47"			
Recommended torque	Nm / lb.in	0.8-1 Nm / 7.1-8.9 lb.in			



Selection

Description	Type	Catalog Number or	Catalog Number	Packaging
Standard block grey	M 6/8	0115 118 11	1SNA 115 811 R1100	50
Standard block blue	M 6/8.N	0125 118 13	1SNA 125 118 R1300	50
Standard block orange	M 6/8	0105 004 22	1SNA 105 004 R2200	50
Standard block yellow	M 6/8	0105 118 20	1SNA 105 118 R2000	50
Standard block beige V0	M 6/8 V0	0195 118 12	1SNA 195 118 R2000	50
Standard block blue V0	M 6/8.N.V0	0199 003 27	1SNA 199 003 R2700	50
Standard block black	M 6/8	0400 239 15	1SNA 400 239 R1500	50
Standard block red	M 6/8	0400 186 21	1SNA 400 186 R2100	50
Standard block white	M 6/8	0400 187 22	1SNA 400 187 R2200	50
Standard block green	M 6/8	0105 128 22	1SNA 105 128 R2200	50
Ground block yellow body/ green marking (without rail contact)	M 6/8.PI	0165 451 21	1SNA 165 451 R2100	50

Accessories

End stop	BAM2	9.9 mm	0206 351 16	1SNA 206 351 R1600	50
End section	grey	FEM6 2.8 mm	0118 368 16	1SNA 118 368 R1600	20
	blue	FEM6 2.8 mm	0128 368 10	1SNA 128 368 R1000	20
	orange	FEM6 2.8 mm	0103 126 16	1SNA 103 126 R1600	20
	yellow	FEM6 2.8 mm	0103 062 21	1SNA 103 062 R2100	20
	green	FEM6 2.8 mm	0103 125 15	1SNA 103 125 R1500	20
	white	FEM6 2.8 mm	0103 312 20	1SNA 103 312 R2000	20
	beige V0	FEM6V0 2.8 mm	0198 368 17	1SNA 198 368 R1700	20
	blue V0	FEM6V0 2.8 mm	0199 302 07	1SNA 199 302 R0700	20
	yellow V0	FEM6V0 2.8 mm	0199 305 02	1SNA 199 305 R0200	20
	black	FEM6 2.8 mm	0107 005 25	1SNA 107 005 R2500	20
Separator end section	grey	SCF6 3 mm	0118 707 03	1SNA 118 707 R0300	20
Assembled jumper bar (with IP20 protection)	2 poles	BJMI8 41 A	0176 669 16	1SNA 176 669 R1600	10
	3 poles	BJMI8 41 A	0176 670 13	1SNA 176 670 R1300	10
	4 poles	BJMI8 41 A	0176 671 00	1SNA 176 671 R0000	10
	5 poles	BJMI8 41 A	0176 672 01	1SNA 176 672 R0100	10
	10 poles	BJMI8 41 A	0176 673 02	1SNA 176 673 R0200	10

10



M 6/8.P - 6 mm² ground block with rail contact - 8 mm .315" spacing

Characteristics

Wire size mm ² / AWG	Solid Stranded	IEC NFC	DIN	UL	CSA
		0.5 - 10		22-8 AWG	24-8 AWG
		0.5 - 6			
Short circuit current	A / s	720A/1s			
Rated wire size	mm ² / AWG	6 mm ²	8 AWG	8 AWG	
Wire stripping length	mm / inches	12 mm / .47"			
Recommended torque	Nm / lb. in	0.8-1 Nm / 7.1-8.9 lb.in			

Selection

Description	Type	Catalog Number	or	Catalog Number	Packaging
Ground block V2 green/yellow	M 6/8.P	0165 114 17		1SNA 165 114 R1700	50
Mounting on rail DIN 3 without screw :					
Ground block V2 green/yellow	D 6/8.P	0165 830 21		1SNA 165 830 R2100	50

Accessories

End section	yellow	FEM6 2.8 mm	0103 062 21	1SNA 103 062 R2100	20
	yellow V0	FEM6 V0 2.8 mm	0199 305 02	1SNA 199 305 R0200	20
Separator end section	grey	SCF6 3 mm	0118 707 03	1SNA 118 707 R0300	20