

ELA IND NX Unit Accessories

FEATURES & SPECIFICATIONS

INTENDED USE

To be powered by 6, 12 or 24 volt battery equipment as part of an emergency lighting system providing light for the path of egress. Ideal for damp and wet location areas requiring remote lighting.

CONSTRUCTION

Single or twin heads available. Fully adjustable lamp heads meet all aiming requirements. Constructed of UV-stabilized thermoplastic with a UL94V-0 flame rating. Fully gasketed mounting plate. Removable bezel and sealed, phosphor-bronze slip-on lamp terminals.

INSTALLATION

Universal mounting plate for use with single or twin-head applications.

Lamp: Glass sealed-beam PAR36 lamp(s).

Dimensions:

Mounting base: 3-1/8"W (79mm) x 5"H (127mm)

Single: 7-3/4"H (197mm) x 4-3/4"W (121mm) x 4-9/16"D (116mm)

Twin: 6-5/8" (168mm) x 13" (330mm) x 3-11/16" (93mm)

LISTINGS

Listed for wet location in accordance with UL1598.

Note: Specifications subject to change without notice.

Actual performance may differ as a result of end-user environment and application.

Catalog Number
Notes
Type

Unit Accessories

ELA NX

Sealed Remote Fixture



(white)

Specifications

Shipping Weight : 1 lb (0.45 kg)

ORDERING INFORMATION

For shortest lead times, configure product using standard options (**shown in bold**).

Example: ELA NX H1212

ELA			NX	
Series	Housing color	Number of heads	Fixture	Lamp type
ELA	(blank) Gray W White B Black	(blank) Single T Twin	NX Sealed and gasketed PAR36	<u>PAR36 sealed-beam</u> Incandescent N0806 8W/6V N1206 12W/6V N1212 12W/12V N1812 18W/12V N2512 25W/12V N3512 35W/12V <u>Halogen</u> H0606 6W/6V H0806 8W/6V H1206 12W/6V H0812 8W/12V H1212 12W/12V H3512 35W/12V H5012 50W/12V