





## Accessories for 16A – 125A non-fusible disconnect switches Base & DIN rail mounted, door mounted

### Base and DIN rail mounted switches



### Auxiliary contacts — snap-on mounting

Description	For use on:	AC thermal amp rating	AC rated voltage	Catalog number	List price
1 N.O. mounts on right side (2 max)	OT16F(T)3 - OT100F(T)3 OT16F3C - OT100F3C	10	600	OA1G10	
1 N.O. Gold plated	OT16F(T)3 - OT100F(T)3	10	600	OA1G10AU	
1 N.O. mounts on left side (2 max)	OT16F3C - OT100F3C	10	600	OA7G10	
1 N.C. mounts on left side (2 max)	OT16F(T)3 - OT100F(T)3 OT16F3C - OT100F3C	10	600	OA1G01	
1 N.C. Gold plated	OT16F(T)3 - OT100F(T)3	10	600	OA1G01AU	
1 N.C. mounts on right side (2 max)	OT16F3C - OT100F3C	10	600	OA8G01	
1 N.O. + 1 N.C. mounts on left or right hand side of switch	OT16F3 - OT100F3	10	600	OA2G11 <sup>①</sup>	

① OT16\_40: max. 2NO+2NC, OT63...100: max 4NO+4NC

### Auxiliary contacts top mounted<sup>②</sup>

- OEZNP1 mounting base required to mount auxiliary contacts (order separately) max 6 aux. blocks. Early break type

Description	For use on:	AC thermal amp rating	AC rated voltage	Catalog number	List price
1 N.O.	OT160E3	10	600	OBEA10	
1 N.C.		10	600	OBEA01	
1 N.O. gold plated		10	600	OBEA-10AU	
1 N.C. gold plated		10	600	OBEA-01AU	
Mounting base on top	OBEA_			OEZNP1	

### Auxiliary contacts side mounted<sup>②</sup>

- Accepts four contacts maximum (2 blocks/side)

Description	For use on:	AC thermal amp rating	AC rated voltage	Catalog number	List price
1 N.O. + 1 N.C.	OT160E3	10	600	OA2G11	
Mounting base required for OA2G11				OAZX1	

② When using OBEA\_ auxiliary contacts, mounting base OEZNP1 is required, and when using OA2G11, mounting base OAZX1 is required.

General information : 1.1 – 1.7    Complete Non-fusible switches: 1.8 – 1.9    Components: 1.10 – 1.26    Technical information: 1.28 – 1.35    Dimensions: 1.36 – 1.53

1.14 Discount schedule DS-H