

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

For use with frame-in LP6 and housings LC6, LI6, L7X, L7XR, L7XF, L7XFR and LI6F.

CONSTRUCTION

Aluminum one piece reflector.

White polyester powder coat paint with clear anodized upper reflector.

Metal baffles available in black or white.

White finish has integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

Rough-ins with clips retain trims.


LISTING

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

6" Full Reflector Trim

6B3



PREMIUM METAL BAFFLE
Narrow Flange


Specifications

Height: 7-3/8 (18.7)

Lamp opening: 6 (15.2)

Diameter: 7-5/8 (19.4)

Trim height when used with
Non-IC incandescent rough-in



All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **6B3W**

6B3	
Series	Finish
6B3	(blank) Black premium baffle/white reflector W White premium baffle/white reflector

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	100 PAR38	LI6
		65 BR40	LI6
		75 A19	LI6
	Fluorescent	13 DTT	L7XF
		18 TRT	LI6F
		26 TRT	L7XF, L7XFR
Non-IC	Incandescent	150 PAR38	LP6, LC6, L7X, L7XR
		120 BR40	LP6, LC6, L7X, L7XR
		150 A19	LP6
		100 A19	LC6, L7X, L7XR