

EKI-75261

16-port Unmanaged Industrial Ethernet Switch with Wide Temperature Range



Features

- Provides 16 10/100 Mbps Ethernet ports with RJ45 connector
- Supports Auto Negotiation and Auto MDI/MDI-X
- Provides flexible mounting: DIN-rail and Wall mount
- Supports Dual 12 ~ 48 V_{DC} power input and 1 relay output
- Supports wide operating temperature -40~75°C

Introduction

EKI-75261 are cost effective unmanaged industrial Ethernet switches which support 16 x 10/100Base-TX fast Ethernet ports.. The long MTBF (Mean Time Between Failures) ensures low operation and maintenance costs. All Ethernet ports have memory buffers that support the store-and-forward mechanism, which assures that data can be transmitted properly. EKI-75261 supports advanced network standards to optimize network performance, reduce maintenance costs, and secure network safety..

Specifications

Communications

- **Standard** IEEE 802.3, 802.3u, 802.3x
- **LAN** 10/100Base-T (X), Optional 100Base-FX
- **Transmission Distance** Ethernet: Up to 100 m (4- wire Cat.5e)
Multi-mode Fiber: Up to 2 km
- **Transmission Speed** Ethernet:10/100 Mbps Auto-Negotiation

Interface

- **Connectors** 16 x RJ45 (Ethernet)
6-pin removable screw terminal (Power & Relay)
- **LED Indicators** System: PWR1, PWR2, P-Fail
10/100T (X): Link/Activity, Duplex/Collision

Power

- **Power Consumption** Max. 8.9 W
- **Power Input** 12 ~ 48 V_{DC}, redundant dual inputs
- **Fault Output** 1 Relay Output

Mechanism

- **Dimensions (W x H x D)** 79 x 152 x 105 mm (3.11" x 5.98" x 4.13")
- **Enclosure** IP30, Metal shell with solid mounting kits
- **Mounting** DIN-rail, Wall

Protection

- **Reverse Polarity** Present
- **Overload Current** Present

Environment


- **Operating Temperature** -40 ~ 75°C (-40 ~ 167°F)
- **Storage Temperature** -40 ~ 85°C (-40 ~ 185°F)
- **Operating Humidity** 5 ~ 95% (non-condensing)
- **Storage Humidity** 0 ~ 95% (non-condensing)
- **MTBF** 237,130 hours

Certification

- **Safety** UL 508
- **EMI** FCC Part 15 Subpart B Class A, EN 55022 Class A
- **EMS** EN 61000-4-2
EN 61000-4-3
EN 61000-4-4
EN 61000-4-5
EN 61000-4-6
EN 61000-4-8
- **Shock** IEC 60068-2-27
- **Freefall** IEC 60068-2-32
- **Vibration** IEC 60068-2-6

Dimensions

Unit: [mm]



Panel Cut-out Dimensions: 115.2 x 152 x 78.6 mm (4.54" x 5.99" x 3.1")

Ordering Information

- EKI-7526I 16FE Unmanaged Ethernet Switch w/Wide Temp