

# Screw Connection Terminal Blocks

## Mini Blocks

	1492-WM3				1492-WM4				1492-WMD1		
Dimensions are not intended to be used for manufacturing purposes. <b>Note:</b> Height dimension is measured from top of rail to top of terminal block.											
	1.14" (29 mm)				1.26" (32 mm)				1.76" (44.6 mm)		
<b>Specifications</b>	Single-circuit mini terminal block.				Single-circuit mini terminal block.				Two-circuit mini terminal block.		
<b>Certifications</b>											
<b>Voltage Rating</b>	300V AC/DC	500V AC/DC	300V AC/DC	420V AC/DC	300V AC/DC	500V AC/DC	300V AC/DC	420V AC/DC	300V AC/DC	300V AC/DC	500V AC/DC
<b>Maximum Current</b>	15 A	24 A	15 A	24 A	20 A	32 A	20 A	32 A	15 A	15 A	17.5 A
<b>Wire Range (Rated Cross Section)</b>	#30...14 AWG	0.5...2.5 mm <sup>2</sup>	#22...14 AWG	2.5 mm <sup>2</sup>	#22...12 AWG	0.5...4.0 mm <sup>2</sup>	#22...12 AWG	4.0 mm <sup>2</sup>	#22...16 AWG	0.5...1.5 mm <sup>2</sup>	
<b>Wire Strip Length</b>	0.24 in. (6 mm)				0.39 in. (10 mm)				0.35 in. (9 mm)		
<b>Recommended Tightening Torque</b>	4.2...4.6 lb•in (0.47...0.52 N•m)				4.7...6.2 lb•in (0.53...0.70 N•m)				4.2...4.6 lb•in (0.47...0.52 N•m)		
<b>Density</b>	61 pcs/ft (200/m)				50 pcs/ft (166/m)				61 pcs/ft (200/m)		
<b>Housing Temperature Range</b>	-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)				-40...+195 °F (-40...+90 °C)		
<b>Terminal Blocks</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Pkg Qty.</b>
<b>Color:</b>	Grey	1492-WM3	50		1492-WM4	50		1492-WMD1	50		50
	Red	1492-WM3-RE	50		1492-WM4-RE	50		1492-WMD1-RE	50		50
	Blue	1492-WM3-B	50		1492-WM4-B	50		1492-WMD1-B	50		50
	Black	1492-WM3-BL	50		1492-WM4-BL	50		1492-WMD1-BL	50		50
	Green	1492-WM3-G	50		1492-WM4-G	50		1492-WMD1-G	50		50
	Yellow	1492-WM3-Y	50		1492-WM4-Y	50		1492-WMD1-Y	50		50
	Orange	1492-WM3-OR	50		1492-WM4-OR	50		1492-WMD1-OR	50		50
	Brown	1492-WM3-BR	50		1492-WM4-BR	50		1492-WMD1-BR	50		50
	White	1492-WM3-W	50		1492-WM4-W	50		1492-WMD1-W	50		50
<b>Accessories</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Cat. No.</b>	<b>Pkg Qty.</b>		<b>Pkg Qty.</b>
<b>Mounting Rails:</b> 1 m Sym. mini DIN (Steel)		1492-DR3	5		1492-DR3	5		1492-DR3	5		5
<b>End Barrier</b>		1492-EBM3	50		1492-EBM4	50		1492-EBMD1	50		50
<b>End Anchors and Retainers:</b> Mini Screwless End Retainer		1492-ERL15	20		1492-ERL15	20		1492-ERL15	20		20
<b>Mini DIN Anchor — Normal Duty</b>		1492-EAJ15	50		1492-EAJ15	50		1492-EAJ15	50		50
<b>Jumpers:</b> Insulated Side Jumper		1492-SJM5-10 (10-pole)	10		1492-N42 (2-pole) 1492-SJ6-10 (10-pole)	50 10		—	—		—
Side Jumper — 12-pole uninsulated		—	—		—	—		1492-SJMD5-12 (Uninsulated)	10		10
Center Jumper — 50-pole		—	—		1492-CJD6-50	5		—	—		—
Center Jumper — 10-pole		1492-CJM5-10	10		1492-CJD6-10	10		—	—		—
Center Jumper — 5-pole		—	—		1492-CJD6-5	10		—	—		—
Center Jumper — 4-pole		—	—		1492-CJD6-4	10		—	—		—
Center Jumper — 3-pole		1492-CJM5-3	10		1492-CJD6-3	10		—	—		—
Center Jumper — 2-pole		1492-CJM5-2	10		1492-CJD6-2	10		—	—		—
Center Jumper Link		1492-CJL5	10		1492-CJL6	10		—	—		—
<b>Other Accessories:</b> Partition Plate		1492-PPM3	50		1492-PPM3	50		1492-PPMD1	50		50
Test Plug		—	—		1492-TP28	10		—	—		—
Test Plug Adapter		1492-TA285	10		1492-TA40	10		—	—		—
Electrical Warning Plate (4-pole)		—	—		1492-EWP6-4	10		—	—		—
<b>Marking Systems:</b> Snap-in Marker Card		1492-MS5X5 (80/card)	5		1492-MS6X9 (80/card)	5		1492-MS5X5 (80/card)	5		5

# IEC Terminal Block Accessories

## Jumpers

### Screw Type Center Jumpers



For Use With	Pkg Qty.	Cat. No.
1492-J3, JD3..., JDG3..., J2Q, J3TW, J3F, JD3F	50	<b>1492-CJJ5-2</b>
	50	<b>1492-CJJ5-3</b>
	50	<b>1492-CJJ5-4</b>
	20	<b>1492-CJJ5-10</b>
1492-J4, J4M	50	<b>1492-CJJ6-2</b>
	50	<b>1492-CJJ6-3</b>
	50	<b>1492-CJJ6-4</b>
	20	<b>1492-CJJ6-10</b>
1492-J6	50	<b>1492-CJJ8-2</b>
	50	<b>1492-CJJ8-3</b>
	50	<b>1492-CJJ8-4</b>
	20	<b>1492-CJJ8-10</b>
1492-J10	50	<b>1492-CJJ10-2</b>
	50	<b>1492-CJJ10-3</b>
	50	<b>1492-CJJ10-4</b>
	20	<b>1492-CJJ10-10</b>
1492-J16	20	<b>1492-CJJ12-2</b>
	20	<b>1492-CJJ12-3</b>
	20	<b>1492-CJJ12-4</b>
	10	<b>1492-CJJ12-10</b>
1492-J35	20	<b>1492-CJJ16-2</b>
	20	<b>1492-CJJ16-3</b>
	20	1492-CJJ16-4
	10	<b>1492-CJJ16-10</b>
1492-J50	10	<b>1492-CJJ18-2</b>
	10	1492-CJJ18-3
	10	1492-CJJ18-4
1492-J70	5	1492-CJJ20-2
	5	1492-CJJ20-3
	5	1492-CJJ20-4
1492-WM3	10	<b>1492-CJM5-2</b>
	10	<b>1492-CJM5-3</b>
	10	1492-CJM5-4
	10	1492-CJM5-5
	10	<b>1492-CJM5-10</b>
1492-W3, WM3, WR3, WTF3..., WTS3...	10	<b>1492-CJL5</b> (Link)
1492-WR3	5	<b>1492-CJD5-50</b>
	10	<b>1492-CJD5-2</b>
	10	<b>1492-CJD5-3</b>
	10	1492-CJD5-4
	10	1492-CJD5-5
	10	<b>1492-CJD5-10</b>

For Use With	Pkg Qty.	Cat. No.
1492-WM4	5	<b>1492-CJD6-50</b>
	10	<b>1492-CJD6-2</b>
	10	<b>1492-CJD6-3</b>
	10	1492-CJD6-4
	10	1492-CJD6-5
	10	<b>1492-CJD6-10</b>
1492-WM4, W4TW	10	1492-CJLD6 (Link)
1492-W3	10	<b>1492-CJ5-2</b>
	10	<b>1492-CJ5-3</b>
	10	<b>1492-CJ5-10</b>
	20	<b>1492-CJCW5</b> (CJ Cover)*
1492-WTF3..., WTS3...	5	<b>1492-CJT5-50</b>
	10	<b>1492-CJT5-2</b>
	10	1492-CJT5-3
	10	1492-CJT5-4
	10	1492-CJT5-5
1492-W4, W4TW	5	<b>1492-CJ6-50</b>
	10	<b>1492-CJ6-2</b>
	10	<b>1492-CJ6-3</b>
	10	<b>1492-CJ6-4</b>
	10	<b>1492-CJ6-5</b>
	10	<b>1492-CJ6-10</b>
1492-W4	10	<b>1492-CJL6</b> (Link)
1492-W4, W6, W10	20	<b>1492-CJCW6</b> (CJ Cover)
1492-W6	5	<b>1492-CJ7-40</b>
	10	<b>1492-CJ7-2</b>
	10	<b>1492-CJ7-3</b>
	10	<b>1492-CJ7-4</b>
	10	1492-CJ7-5
1492-W6	10	<b>1492-CJ7-10</b>
1492-W6	10	1492-CJL7 (Link)
1492-W10	5	<b>1492-CJ8-40</b>
	10	<b>1492-CJ8-2</b>
	10	<b>1492-CJ8-3</b>
	10	1492-CJ8-4
1492-W10	10	1492-CJ8-5
	10	<b>1492-CJ8-10</b>
	10	<b>1492-CJL8</b> (Link)
1492-W16S	10	<b>1492-CJS11-2</b>
	10	<b>1492-CJS11-3</b>
	10	1492-CJS11-4
	10	<b>1492-CJS11-5</b>
	10	<b>1492-CJS11-10</b>

Note: Notching out one or more jumper poles, with the notched jumpers going across different potentials, will require de-rating to 400V.

\* May only be used as a marking surface. May not be installed over center jumper.

