


3-Position Selector Switch Operators, Illuminated ‡



Standard Knob
 Cat. No. 800FP-LSM37

Switching Angle



Target Table and Operator Position (60° Switching Angle)				
Contact Type*	Position on Mounting Latch			
N.O.	Left	X	O	O
	Right	O	O	X
N.C.	Left	O	X	X
	Right	X	X	O

Note: X = Closed/O = Open

* Contact selection is limited to the following options, consult your local Rockwell Automation sales office or Allen-Bradley distributor for other options.

Operator Type 	Pkg. Quantity	Green		Red		Yellow	
		Plastic Cat. No.	Metal Cat. No.	Plastic Cat. No.	Metal Cat. No.	Plastic Cat. No.	Metal Cat. No.
	1	800FP-LSM33	800FM-LSM33	800FP-LSM34	800FM-LSM34	800FP-LSM35	800FM-LSM35
		800FP-LSR33	800FM-LSR33	800FP-LSR34	800FM-LSR34	800FP-LSR35	800FM-LSR35
		800FP-LSL33	800FM-LSL33	800FP-LSL34	800FM-LSL34	800FP-LSL35	800FM-LSL35
		800FP-LSB33	800FM-LSB33	800FP-LSB34	800FM-LSB34	800FP-LSB35	800FM-LSB35

800F P - LS M3 3 e
 a b c d e

a

Operator Construction	
Code	Description*
P	Round plastic operator (IP66, Type 4/4X/13)
M	Round metal operator (IP66, Type 4/13)

b

Operator Type	
Code	Description
LS	Standard knob
LH	Knob lever§

c

Operator Function	
Code	Type
M3	Maintained
L3	Spring return from left
R3	Spring return from right
B3	Spring return from left and right

d

Knob/Insert Color		
Code	Knob Color	Insert Color
0	Amber➤	White
3	Green	White
4	Red	White
5	Yellow➤	Black
6	Blue➤	White
7	Clear	Black

e

Orientation	
Code	Description
Blank	Standard
N	90° offset*

* LED module required for illumination, can not use incandescent module.
 * For use in vertical mount 800F enclosures.
 ‡ Crevices may exist on product that may be unsuitable for certain applications. Please consult your local Rockwell Automation sales office or Allen-Bradley distributor.
 § Only available in clear.
 ➤ Use of a white LED is recommended.