




# Spring-Clamp Connection Terminal Blocks

## Plug-in Style Blocks

	1492-LD32P			1492-LG31P			1492-LG3T1P		
<p>Dimensions are not intended to be used for manufacturing purposes.                      Note: Height dimension is measured from top of rail to top of terminal block.</p>   									
<b>Specifications</b>	Two-circuit terminal block with 1 fixed and 1 plug-in connection on each level. Plug-in connectors can be individual or grouped configurations.			Single-circuit grounding terminal block with 1 fixed and 1 plug-in connection.			Single-circuit grounding terminal block with 2 fixed and 1 plug-in connection.		
<b>Certifications</b>		CSA	IEC		CSA	IEC		CSA	IEC
<b>Voltage Rating</b>	300V AC/DC		500V AC/DC	—		—	—		—
<b>Maximum Current</b>	20 A		24 A	Grounding		—	Grounding		—
<b>Limited Rating - Voltage*</b>	600V AC/DC		—	—		—	—		—
<b>Limited Rating - Current*</b>	5 A		—	—		—	—		—
<b>Wire Range (Rated Cross Section)</b>	26... 12 AWG		0.5...2.5 mm <sup>2</sup>	26... 12 AWG		0.5...2.5 mm <sup>2</sup>	26... 12 AWG		0.5...2.5 mm <sup>2</sup>
<b>Wire Strip Length</b>	0.394 in (10 mm)			0.394 in (10 mm)			0.394 in (10 mm)		
<b>Density</b> (Blocks per ft/m)	59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)			59 pcs/ft (196 pcs/m)		
<b>Housing Temperature Range</b>	-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)			-58...+248 °F (-50...+120 °C)		
<b>Terminal Blocks</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>
<b>Color</b>	Grey	1492-LD32P	50	—	—	—	—	—	—
	Green/Yellow	—	—	1492-LG31P	50	—	1492-LG3T1P	50	—
<b>Accessories</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>	<b>Pcs/Pkg</b>	<b>Cat. No.</b>
<b>Mounting Rails</b>									
1 m Symmetrical DIN (Steel)	<b>199-DR1</b>	10	<b>199-DR1</b>	10	<b>199-DR1</b>	10	<b>199-DR1</b>	10	<b>199-DR1</b>
1 m Symmetrical DIN (Aluminum)	<b>1492-DR5</b>	10	<b>1492-DR5</b>	10	<b>1492-DR5</b>	10	<b>1492-DR5</b>	10	<b>1492-DR5</b>
1 m Hi-Rise Sym. DIN (Aluminum)	<b>1492-DR6</b>	2	<b>1492-DR6</b>	2	<b>1492-DR6</b>	2	<b>1492-DR6</b>	2	<b>1492-DR6</b>
1 m Angled Hi-Rise Sym. DIN (Steel)	<b>1492-DR7</b>	2	<b>1492-DR7</b>	2	<b>1492-DR7</b>	2	<b>1492-DR7</b>	2	<b>1492-DR7</b>
<b>End Barrier</b>	Grey	1492-EBLD32P	50	—	—	—	—	—	—
	Yellow	—	—	1492-EBL31P-Y	50	—	1492-EBL3T1P-Y	50	—
<b>End Anchors</b>									
Screwless End Retainer	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>	20	<b>1492-ERL35</b>
<b>DIN Rail - Normal Duty</b>	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>	100	<b>1492-EAJ35</b>
<b>Din Rail - Heavy Duty</b>	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>	50	<b>1492-EAHJ35</b>
<b>Jumpers</b>									
Plug-in Center Jumper — 50 Pole	<b>1492-CJLJ5-50</b>	10	—	—	—	—	—	—	—
Plug-in Center Jumper — 10 Pole	<b>1492-CJLJ5-10</b>	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 9 Pole	1492-CJLJ5-9	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 8 Pole	<b>1492-CJLJ5-8</b>	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 7 Pole	<b>1492-CJLJ5-7</b>	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 6 Pole	<b>1492-CJLJ5-6</b>	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 5 Pole	<b>1492-CJLJ5-5</b>	20	—	—	—	—	—	—	—
Plug-in Center Jumper — 4 Pole	<b>1492-CJLJ5-4</b>	60	—	—	—	—	—	—	—
Plug-in Center Jumper — 3 Pole	<b>1492-CJLJ5-3</b>	60	—	—	—	—	—	—	—
Plug-in Center Jumper — 2 Pole	<b>1492-CJLJ5-2</b>	60	—	—	—	—	—	—	—
<b>Individual Plug-in Connector</b>	Grey	1492-STP	50	—	—	—	—	—	—
	Green	1492-STP-G	50	1492-STP-G	50	—	1492-STP-G	50	—
<b>Ganged Connector - Start Plug</b>	Grey	1492-SBSTP	50	—	—	—	—	—	—
<b>Ganged Connector - Middle Plug†</b>	Grey	1492-GSTP	50	—	—	—	—	—	—
<b>Ganged Connector - End Plug</b>	Grey	1492-EBSTP	50	—	—	—	—	—	—
<b>Plug-In Component Accessories</b>									
Locking Element	Yellow	1492-STPLE	25	1492-STPLE	25	—	1492-STPLE	25	—
Coding Element	Yellow	1492-STPCE	50	1492-STPCE	50	—	1492-STPCE	50	—
Strain Relief	Yellow	1492-STPSR	25	1492-STPSR	25	—	1492-STPSR	25	—
<b>Group Marking</b>									
Rail Mount Group Marking Carrier	<b>1492-GM35</b>	25	<b>1492-GM35</b>	25	<b>1492-GM35</b>	25	<b>1492-GM35</b>	25	<b>1492-GM35</b>
End Anchor Top Marker Carrier*	<b>1492-GMC</b>	50	<b>1492-GMC</b>	50	<b>1492-GMC</b>	50	<b>1492-GMC</b>	50	<b>1492-GMC</b>
Cat. No. 1492-GMC Top Marker Tag	<b>1492-M5X30(20/card)</b>	5	<b>1492-M5X30(20/card)</b>	5	<b>1492-M5X30(20/card)</b>	5	<b>1492-M5X30(20/card)</b>	5	<b>1492-M5X30(20/card)</b>
<b>Marking Systems</b>									
Snap-in Marker Cards	<b>1492-MR5X12 (120/card)</b>	5	<b>1492-MR5X12 (120/card)</b>	5	<b>1492-MR5X12 (120/card)</b>	5	<b>1492-MR5X12 (120/card)</b>	5	<b>1492-MR5X12 (120/card)</b>
Snap-In Marker Cards	<b>1492-MR5X8 (120/card)</b>	5	<b>1492-MR5X8 (120/card)</b>	5	<b>1492-MR5X8 (120/card)</b>	5	<b>1492-MR5X8 (120/card)</b>	5	<b>1492-MR5X8 (120/card)</b>








\* The Bulletin 1492-GMC marker carrier installs directly on the top of a 1492-EAJ35 end anchor or a 1492-ERL35 end retainer for group marking purposes.

\* Blocks contain dual UL/CSA listings and can be used at 300V with a 20 A rating or 600V with a 5 A rating.

† For ganged configurations greater than 2, use multiple 1492-GSTP plug-in blocks.



**Blank Markers**

Photo	For Use With	Markers per Card	Marker Size	Pkg Qty.	Cat. No.
<p>Snap-In Individual Markers 1492-M</p>   	1492-L	100	3 x 5 mm	5	<b>1492-M3X5</b>
	1492-L	120	3 x 12 mm	5	<b>1492-M3X12</b>
	1492-J, L	200	5 x 5 mm	5	<b>1492-M5X5</b>
		144	5 x 8 mm	5	<b>1492-M5X8</b>
		144	5 x 10 mm	5	<b>1492-M5X10</b>
		144	5 x 12 mm	5	<b>1492-M5X12</b>
		96	5 x 15 mm	5	<b>1492-M5X15</b>
		20	5 x 30 mm	5	* <b>1492-M5X30</b>
	1492-J, L	200	6 x 5 mm	5	<b>1492-M6X5</b>
		120	6 x 10 mm	5	<b>1492-M6X10</b>
	1492-J, L, 1738 ArmorPoint™	120	6 x 12 mm	5	<b>1492-M6X12</b>
	1492-J, L	108	7 x 12 mm	5	<b>1492-M7X12</b>
		160	8 x 5 mm	5	<b>1492-M8X5</b>
	NEMA (1492-HM1, -HM2, -HM3) Terminal Blocks, 1492-CB Circuit Breakers	120	6 x 10 mm	5	<b>1492-MN81</b>
	NEMA (1492-HM3) Terminal Blocks, 1492-CB Circuit Breakers	40	10 x 10 mm	5	<b>1492-MN83</b>
	1492-W,R, 700-HA Relays	56	8 x 9 mm	5	<b>1492-MS8X9</b>
56		8 x 12 mm	5	<b>1492-MS8X12</b>	
700-HN204, -HN205, Relay Sockets	40	8 x 17 mm	5	<b>1492-MS8X17</b>	
1667 PanelConnect™	40	9 x 20 mm	5	<b>1492-MS9X20</b>	
100-C, -D Contactors, 700-CF Relays, 140 Circuit Breakers, 193-E1, -E3	40	10 x 17 mm	5	<b>1492-MS10X17</b>	
<p>Snap-In Linked Markers 1492-MR</p> 	1492-J, -L	120	5 x 8 mm	5	<b>1492-MR5X8</b>
		120	6 x 8 mm	5	<b>1492-MR6X8</b>
		120	5 x 12 mm	5	<b>1492-MR5X12</b>
		120	6 x 12 mm	5	<b>1492-MR6X12</b>
		84	8 x 12 mm	5	<b>1492-MR8X12</b>
			1492-WM3, -WMD1	80	5 x 5 mm
1492-W, 700-HA, 800F Contact Block	80		5 x 9 mm	5	<b>1492-MS5X9</b>
1492-W, 700-H Relays	80		5 x 12 mm	5	<b>1492-MS5X12</b>
1492-W, -R, 700-H Relays	80		6 x 9 mm	5	<b>1492-MS6X9</b>
1492-W, 700-H Relays	80		6 x 12 mm	5	<b>1492-MS6X12</b>
<p>Snap-In Hinged Markers</p> 	1492-L	96	5 x 10 mm	5	<b>1492-MH5X10</b>
		96	5 x 15 mm	5	<b>1492-MH5X15</b>
		80	6 x 12 mm	5	<b>1492-MH6X12</b>
<p>Cable Markers 1492-MW</p> 	<b>External Diameter (mm)</b>	<b>Markers per Card</b>	<b>Marker Size</b>	<b>Pkg. Qty.</b>	<b>Cat. No.</b>
	from 0.276 in. (from 7.0 mm)	32	9 x 24 mm*	5	<b>1492-MW9X24</b>
	from 0.276 in. (from 7.0 mm)	32	5 x 23 mm*	5	1492-MW10X23
	from 0.276 in. (from 7.0 mm)	32	8 x 23 mm*	5	1492-MW14X23
	from 0.276 in. (from 7.0 mm)	12	11 x 44 mm*	5	<b>1492-MW11X60</b>
	0.162...0.193 in. (4.1...4.9 mm)	32	5 x 21 mm‡	5	1492-MW5-21
	0.185...0.229 (0.268) in. (4.7...5.8 [6.8] mm)	32	6 x 21 mm‡	5	1492-MW6-21
	0.229...0.276 (0.335) in. (5.8...7.0 [8.5] mm)	32	7 x 21 mm‡	5	1492-MW7-21

\* Requires cable ties.  
 \* Requires Cat. No. 1492-GMC  
 ‡ Requires Cat. No. 1492-PLOTPLTA