



Description

The Guardmaster 440G-LZ is a guard-locking interlock switch for use on partial body access guards. It has a rated holding force of 1,300N. The switch functions by a locking bolt extending into the actuator preventing the opening of a guard. It has two OSSD solid-state outputs that are only enabled when the locking bolt is extended and detected as entered into the actuator. The locking bolt will only attempt to extend when the correct actuator is detected. It can be used as part of a guard locking system to achieve performance Level "e" to EN/ISO 13849-1 and certified by the TÜV as meeting EN/ISO 13849-1 performance level "e" for both position and lock monitoring.

Advanced algorithms and a bi-stable solenoid result in low energy use. Peak power only occurs when changing from unlocked to locked (or vice versa). The bi-stable drive uses minimal power and will not produce heat when either locked or unlocked. The functionality is configured to replicate a traditional power-to-release or power-to-lock device

The RFID actuators can be selected as either standard or uniquely coded. The user can select the level of actuator coding according to the foreseeable risk of tampering in accordance with the requirements of EN/ISO 14119:2013

Each switch has semiconductor OSSD safety outputs that can be connected in series with other safety components that also have OSSD solid-state outputs. On-board twin LEDs enable visual diagnostics. An auxiliary output is also included as well as a manual release.

This switch can be used in washdown applications as found in the food and beverage, pharmaceutical, and semiconductor industries because of its IP69k rating with stainless steel metal parts and a design that is hygiene compliant.



ATTENTION: With the 440G-LZ "power-to-lock" style, provisions may be required to ensure that a dangerous situation can not result from open circuit faults or power cuts.

Features

- Certified to PLe to EN/ISO 13849-1 (both for door position and lock monitoring to EN/ISO 14119)
- Solid-state design and monitored outputs
- Scalable protection with unique or standard coded RFID actuators
- High holding force of 1,300 N (Fzh)
- Energy efficient green device that only uses 2.5 W
- IP69k and hygienic design
- Power-to-release and power-to-lock versions
- Compact design optimized for ease of mounting
- Diagnostic information provided by two bright 270° LEDs
- Solid-state OSSD outputs series connectable to EN/ISO 14119:2013

Specifications

| Safety Ratings | |
|--|---|
| Standards | IEC 60947-5-3, IEC 60947-5-1, IEC 61508, EN ISO 13849-1, IEC 62061, ISO 14119, UL 508 |
| Safety Classification | PLe Category 4 per ISO 13849-1, SIL 3 per IEC 61508 and IEC 62061 |
| Functional Safety Data Guard door sensing and lock monitoring | PFHd: 9.1×10^{-10} ; Dual channel interlock can be suitable for use in application up to PLe (according to ISO 13849-1) and for use up to SIL3 systems (according to IEC 62061 and IEC 61508) depending on application characteristics. Mission time/PTI: 20 years |
| Certifications | CE Marked for all applicable EU directives, cULus (UL 508), TÜV, C-tick |
| Operating Characteristics | |
| Torque for M5 mounting of switch and actuator mounting bracket | 2 Nm max. |
| Locking bolt insertion for assured locking & holding force | Min. of 5 mm (0.19 in.), max. of 10 mm (0.39 in.) |
| Locking bolt alignment tolerance X, Y, Z | Max. of ± 2.5 mm (0.09 in.) |
| Holding Force Fmax (EN/ISO 14119) | 1,690 N |
| Holding Force Fzh (EN/ISO 14119) | 1,300 N |
| Maximum output current (each outputs) | 200 mA |
| Quiescent power consumption, locked or unlocked | 2.5 W |
| Peak current and duration, at turn on or after lock/unlock operation | 400 mA / 100 ms |
| Operating voltage Ue | 24V DC +10% / -15% Class 2 SELV |
| Maximum frequency of operating cycles | 0.2 Hz |
| Dwell time between subsequent locking/unlocking | 2.5 s |
| Response time (Off) | 100 ms first switch, 50 ms additional for each switch |
| Risk Time (according to IEC 60947-5-3) | 100 ms |
| Start up time (availability) | 5 s |
| Maximum length of a chain of switches | 10 km (Dependent on cable/connection/required response time) |
| Utilization category (IEC 60947-5-2) | DC-13 24V 200 mA |
| Insulation voltage Ui (IEC 60947-1) | 75V |
| Impulse withstand voltage Uimp (IEC 60947-1) | 1 kV |
| Pollution degree (IEC 60947-1) | 3 |
| Manual (auxiliary) release | Built in |
| Protection class (IEC 61140) | Class II |
| Mechanical life | 500,000 cycles |
| Outputs (Guard door closed and locked) | |
| Safety Outputs | 2 x PNP, 0.2 A max / ON (+24V DC) |
| Auxiliary Outputs | 1 x PNP, 0.2 A max / OFF (0V DC) |
| Environmental | |
| Operating temperature [C (F)] | 0...+55° (+14...+131°) |
| Storage temperature [C (F)] | -25...+75° (-13...+167°) |
| Operating humidity | 5...95% relative |
| Enclosure ingress rating | NEMA 3, 4X, 12, 13, IP66, IP67, IP69k |
| Shock and vibration | IEC 60068-2-27 30 g, 11 ms/IEC 60068-2-6 10...55 Hz |
| Hygienic | ISO 14159:2004 and EN 1672-2005, (for that part of the machine defined as "food splash area") |

3-Interlock Switches

Safety Switches

Guard Locking Switches

440G-LZ

Specifications (continued)

| Environmental (continued) | |
|---------------------------|---|
| Washdown | Sodium Hydroxide based washdown fluids |
| Radio frequency / EMC | IEC 60947-5-3, FCC-1(Parts 18&15), R&TTE |
| General | |
| Materials | ABS, locking bolt and mounting bracket 304 stainless steel |
| Weight switch/actuator | Switch 400 g, actuator 150 g, actuator mounting bracket 60 g |
| Protection Type | Short-circuit, current limitation, overload, reverse polarity, overvoltage (up to 60V max.), thermal shutdown/restart |

Product Selection

Complete Switch (including switch body, actuator and actuator mounting bracket)

| Locking Type | Actuator Type | Cat. No. | | |
|------------------|---|----------------|----------------|---------------------------------|
| | | Connector Type | | |
| | | 3 m Lead | 10 m Lead | 6-in. Pigtail with M12 8-Pin QD |
| Power to release | Standard (low level to EN/ISO 14119:2013) | 440G-LZS21SPRA | 440G-LZS21SPRB | 440G-LZS21SPRH |
| | Unique (high level to EN/ISO 14119:2013) | 440G-LZS21UPRA | 440G-LZS21UPRB | 440G-LZS21UPRH |
| Power to lock | Standard (low level to EN/ISO 14119:2013) | 440G-LZS21SPLA | 440G-LZS21SPLB | 440G-LZS21SPLH |
| | Unique (high level to EN/ISO 14119:2013) | 440G-LZS21UPLA | 440G-LZS21UPLB | 440G-LZS21UPLH |

Accessories

Spare Actuators


| Locking Type | Actuator Type | Cat. No. |
|------------------|--|-------------|
| Power to release | Standard (low level EN/ISO 14119:2013) | 440G-LZASPR |
| | Unique (high level EN/ISO 14119:2013) | 440G-LZAUPR |
| Power to lock | Standard (low level EN/ISO 14119:2013) | 440G-LZASPL |
| | Unique (high level EN/ISO 14119:2013) | 440G-LZAUPL |

Mounting Brackets


| Description | Cat. No. |
|------------------------------|------------|
| Actuator mounting bracket | 440G-LZAM1 |
| Switch body mounting bracket | 440G-LZAM2 |

Approximate Dimensions

Dimensions are shown in mm (in.). Dimensions are not intended to be used for installation purposes.



Typical Wiring Diagrams



3-Interlock Switches

Guard Locking Switches

440G-LZ

3-Interlock
Switches