




## Insulating Bushings

For Rigid • IMC. Press fit.  
Holds firmly in place while pulling cables.



Example:  
Telephone cable  
protected by Rigid  
insulating bushing.


Meets 2011 NEC code requirements for 300-15(c) protection. Listed for use in environmental air handling spaces per 2011 NEC code requirements 300-22(c).

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	UNIT PKG	STD PKG	DIM A	DIM B
RGD50	51930	1/2	100	1000	.531	.989
RGD75	51932	3/4	100	1000	.531	1.185
RGD100	51933	1	100	100	.625	1.542
RGD125	51934	1-1/4	100	100	.625	1.891
RGD150	51935	1-1/2	100	100	.625	2.062
RGD200	51936	2	50	50	.625	2.655
EMT250†	12240	2-1/2	25	25	1.225	3.062
EMT300†	12245	3	25	25	1.225	3.690
EMT350†	12250	3-1/2	25	25	1.231	4.187
EMT400†	12255	4	25	25	1.233	4.815



See page B-1 for EMT Insulating Bushings size 1/2" through 4".  
† Can also be used for EMT.



E105706 LR49636



Arlington's Rigid Insulating Bushings protect cables from abrasion by rigid. Examples: Power, Cable TV, computer datalines, telephone/modem, a/v cables, alarm systems, security systems. Rigid is often used to protect cables where damage could occur in a house or building.



Place board over bushing and tap onto Rigid or EMT with hammer.

## Zinc Combination Couplings EMT to Rigid

EMT compression to screw-in flexible metal conduit.  
Zinc die-cast.



2400

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
2400	06920	1/2"	50	50	1.000	1.267	.946
2410	06921	3/4"	50	50	1.000	1.412	1.200
2411	06922	3/4"	50	50	1.210	1.475	1.200

Use with any listed fitting.

