

Screw-In Connectors with Insulated Throat


For flexible metal conduit.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38A | 76381 | 3/8 | 1/2 | 50 | 500 | 1.371 | .470 | 1.140 |
| GF50A | 76501 | 1/2 | 1/2 | 50 | 250 | 1.450 | .710 | 1.140 |
| GF75A | 76751 | 3/4 | 3/4 | 25 | 250 | 1.596 | .930 | 1.390 |
| GF100A | 76101 | 1 | 1 | 25 | 100 | 1.992 | 1.125 | 1.685 |
| GF125A | 76251 | 1-1/4 | 1-1/4 | 10 | 40 | 2.182 | 1.410 | 2.115 |
| GF150A | 76151 | 1-1/2 | 1-1/2 | 10 | 40 | 2.372 | 1.695 | 2.370 |
| GF200A | 76201 | 2 | 2 | 5 | 20 | 2.663 | 2.190 | 2.890 |



E60812 LR49636



Screw-In SNAP-TITE® Connectors

With spring steel clip.
For flexible metal conduit.
Zinc die-cast.




| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38ST | 80162 | 3/8 | 1/2 | 50 | 500 | 1.470 | .475 | 1.055 |
| GF50ST | 80166 | 1/2 | 1/2 | 50 | 250 | 1.468 | .720 | 1.055 |
| GF75ST | 80170 | 3/4 | 3/4 | 25 | 250 | 1.694 | .940 | 1.350 |

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 6.



E60812 LR49636



Screw-In SNAP-TITE® Connectors with Insulated Throat

With spring steel clip.
For flexible metal conduit.
Zinc die-cast.



| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | KO SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|---------|----------|---------|-------|-------|-------|
| GF38AST | 80164 | 3/8 | 1/2 | 50 | 500 | 1.456 | .480 | 1.045 |
| GF50AST | 80168 | 1/2 | 1/2 | 50 | 250 | 1.456 | .727 | 1.045 |

SNAP-TITE® products have been tested and listed by UL in accordance with UL's ground fault requirements. For additional information see page 6.



E60812 LR49636

