



P2484 EG, GR, HG




Wt/100 pcs: 134 Lbs (60.8 kg)

P2484W EG, GR, HG




Wt/100 pcs: 134 Lbs (60.8 kg)

P1130, P1131 EG, GR, HG



Part Number	"A" In (mm)	"B" In (mm)	Wt/100 pcs Lbs (kg)
P1130	6 ⁵ / ₁₆ 168.3	4 101.6	190 86.2
P1131	8 ⁵ / ₁₆ 219.1	6 152.4	242 109.8


P1546, P2094 THRU P2100 EG, GR, HG



Part No.	"A" Degree (rad)	"B" In (mm)	"C" In (mm)
P2094	82½° 1.44	3 ⁹ / ₁₆ 90.5	1 ¹¹ / ₁₆ 42.9
P2095	75° 1.31	3 ⁹ / ₁₆ 90.5	1 ¹¹ / ₁₆ 42.9
P2096	67½° 1.18	3½ 88.9	1¾ 44.5
P2097	60° 1.05	3¾ 85.7	1 ⁷ / ₈ 47.6
P2098	52½° 0.92	3¼ 82.6	2 ¹ / ₁₆ 52.4
P1546	45° 0.79	3 76.2	2 ⁵ / ₁₆ 58.7
P2099	37½° 0.65	3½ 88.9	1 ¹³ / ₁₆ 46.0
P2100	37½° 0.65	2 ¹¹ / ₁₆ 68.3	2 ³ / ₈ 66.7

Wt/100 pcs: 58 Lbs (26.3 kg)


P2101 THRU P2104 EG, GR, HG



Part No.	"A" Degree (rad)	"B" In (mm)
P2101	30° 0.52	3¼ 82.6
P2102	22½° 0.39	3 ⁵ / ₁₆ 84.1
P2103	15° 0.26	3 ⁵ / ₁₆ 84.1
P2104	7½° 0.13	3 ⁵ / ₁₆ 84.1

Wt/100 pcs: 58 Lbs (26.3 kg)


P1186, P2105 THRU P2110 EG, GR, HG



Part Number	"A" Degree (rad)	"B" In (mm)
P2105	82½° 1.44	3¼ 82.6
P2106	75° 1.31	3¼ 82.6
P2107	67½° 1.18	3 ⁷ / ₁₆ 81.0
P2108	60° 1.05	3 ⁷ / ₁₆ 81.0
P2109	52½° 0.92	3 ⁵ / ₁₆ 79.4
P1186	45° 0.79	3 ⁵ / ₁₆ 79.4
P2110	37½° 0.65	3 ⁷ / ₁₆ 77.8

Wt/100 pcs: 58 Lbs (26.3 kg)

P2260 THRU P2270 EG, GR, HG



Part Number	"A" Degree (rad)	"B" In (mm)
P2270	82½° 1.44	3 ⁵ / ₈ 92.1
P2269	75° 1.31	3 ⁵ / ₈ 92.1
P2268	67½° 1.18	3 ⁵ / ₈ 92.1
P2267	60° 1.05	3 ¹¹ / ₁₆ 93.7
P2266	52½° 0.92	3 ¹¹ / ₁₆ 93.7
P2265	45° 0.79	3 ¹¹ / ₁₆ 93.7
P2264	37½° 0.65	3 ¹¹ / ₁₆ 93.7
P2263	30° 0.52	3 ¹¹ / ₁₆ 93.7
P2262	22½° 0.39	3¼ 95.3
P2261	15° 0.26	3¼ 95.3
P2260	7½° 0.13	3¼ 95.3

Wt/100 pcs: 78 Lbs (35.4 kg)

Standard Dimensions for 1⁵/₈" (41.3mm) width series channel fittings (Unless Otherwise Shown on Drawing)

Hole Diameter: 5/16" (14.3mm); Hole Spacing - From End: 13/16" (20.6mm); Hole Spacing - On Center: 1 7/8" (47.6mm); Width: 1 5/8" (41.3mm); Thickness: 1/4" (6.4mm)