

- Die Cast Aluminum Housing
- Borosilicate Glass Lens
- Face Frame Opens to the Side
- Threaded Apertures for Conduit & Photo Control
- Emergency Battery Backup Available



**quick SHIP Products**

CATALOG #	DESCRIPTION	VOLTS	BALLAST TYPE	LAMP
<b>Pulse Start</b>				
WLM-70MHQPK	70 watt PS	Quad	HX-HPF	MH70/U/M
WLM-100MHQPK	100 watt PS	Quad	HX-HPF	MH100/U/M
WLM-150PQPK	150 watt PS	Quad	HX-HPF	MS150/U
<b>High Pressure Sodium</b>				
WLM-100HQPK	100 watt HPS	Quad	HX-HPF	C100S54
WLM-150HPK	150 watt HPS	120	R-NPF	C150S55
WLM-150HQPK	150 watt HPS	Quad	HX-HPF	C150S55
<b>Fluorescent</b>				
WLM-84FEUPK	84 watt FL	Univ.	Prog. Start	(2) PLT42W/41

**Accessories**

CATALOG #	DESCRIPTION	STD. PKG.
280-019-1	Wireguard for WLM	1
280-022-1	Polycarbonate Guard for WLM	1
320-013	Full Cut-Off Shield for WLM-Bronze	1
210-007	WLM Face Frame Assembly-Bronze	1
230-002	Button 120V Photo Control	1
230-008	Button 208-277V Photo Control	1

**Ordering Format**

example: **WLM** - **150** **P** **Q** **PK**

**PRODUCT SERIES**  
WLM = Medium Wall Light

**WATTAGE**  
52 = 52W  
64 = 64W  
70 = 70W  
84 = 84W  
100 = 100W  
150 = 150W

**LAMP TYPE**  
MH = Low Wattage Pulse Start  
P = Pulse Start  
H = High Pressure Sodium  
FE = Fluorescent/Electronic

**BALLAST VOLTAGE**  
Blank = 120V  
Q = Quad Volt  
U = 120-277\* Volt  
\*Fluorescent Only

**WIRING**  
PC = Button Photocell 120  
P2 = Button Photocell 208  
P3 = Button Photocell 240  
P4 = Button Photocell 277

**LAMP OPTION**  
PK = With Lamp  
Blank = No Lamp



**BATTERY**  
EB = Emergency Battery Backup\*  
\*Fluorescent Only

**MH vs. Fluorescent**


	100w MH	84w FL
Lamp Life	10,000 hrs	12,000 hrs
Start Up Time	3-5 minutes	Instant
Restrike Time	15-20 minutes	Instant
CRI	70	82
Color Temperature	4,200k	4,100k
Initial Lumens	7,800	6,400
Mean Lumens	5,600	5,500
Mean Lumens/Watt	43.4	65.52
Watts/Fixture	129	84
Cost/Year*	\$30.13	\$19.62

\*Based On: 8 hours per day | 365 days per year | \$0.08 per kWh

**Dimensions**



**Mounting Detail**



**Photometrics**

150W PS @ 15' Mounting Height

