


BEAM CLAMPS

Finish: Painted Green, or Electro-galvanized **Order By:** No. and Finish **Note:** Use in pairs or with other support




PS 95 – “C” Clamp



Rod Size	A	B	Load Rating	Wt./100 pcs
3/8"	2 5/16"	3/8"	330	35
1/2"	2 1/4"	1/2"	380	41
5/8"	2 3/8"	5/8"	450	67
3/4"	2 1/4"	1/2"	500	72

Material: Steel


PS 86 – “C” Clamp



Rod Size	A	B	Load Rating	Wt./100 pcs
3/8"	1 11/16"	1 3/4"	400	38
1/2"	1 23/32"			52
5/8"	1 15/16"	2"	450	68
3/4"	2 1/32"			600

Material: Malleable Iron, Steel Set Screw

PS 2654 & PS 2654A – Column Attachment



PS 2654 Use with PS 200


PS 2654A Use with PS 500

Slip Rating: 800 lbs.


Note: Column attachment can only be used in pairs.

Weight/100 pcs: 41 lbs.

PS 93 – Universal “C” Clamp



At least one full thread must be exposed





Material: Malleable Iron, Steel Set Screw


Part No.	Rod Size A	DIMENSIONS (Inches)				Max. Pipe Size	Max. Load (Lbs.)	Wt/100 pcs
		B	C	D	E			
PS 93 3/8	3/8	1 5/8	2	3/4	7/8	2	400	28
PS 93 1/2	1/2	1 5/8	2	3/4	7/8	3 1/2	500	34

• Maximum temperature of 450° F

PS 94 – Wide Throat Top Beam “C” Clamp



At least one full thread must be exposed



Material: Malleable Iron, Steel Set Screw

Part No.	Rod Size A	DIMENSIONS (Inches)					Max Pipe Size	Max. Load (Lbs.)	Wt/100 pcs
		B	C	D	E	F			
PS 94 5/8	5/8	1 3/4	2 1/4	3/4	1 1/4	1	5	600	66
PS 94 3/4	3/4	1 7/8	2 3/8	3/4	1 3/8	1 1/4	8	800	83

• Maximum temperature of 450° F