

FL

9" Die Cast Rectangular

**26 - 150 watts
PS | HPS | FL**

SERIES




- Die Cast Aluminum Housing
- Hinged Face Frame
- One Piece Aluminum Reflector
- 1/2" Heavy Duty Knuckle
- UL Listed for Ground Mounting




quick SHIP Products

Dimensions




Mounting Detail



Photometrics

100W MH @ 15' Mounting Height



CATALOG #	DESCRIPTION	VOLTS	BALLAST	LAMP
Pulse Start				
FL-50MHQPK	50 watt PS	Quad	HX-NPF	MH50/U/M
FL-70MHQPK	70 watt PS	Quad	HX-NPF	MH70/U/M
FL-100MHQPK	100 watt PS	Quad	HX-NPF	MH100/U/M
High Pressure Sodium				
FL-70HPK	70 watt HPS	120	R-NPF	C70S62/M
FL-100HPK	100 watt HPS	120	R-NPF	C100S54/M
FL-150HPK	150 watt HPS	120	R-NPF	C150S55/M
Fluorescent				
FL-42FEUPK	42 watt FL	Univ.	Prog. Start	PLT42W/41

Accessories

CATALOG #	DESCRIPTION	STD. PKG.
210-001	FL Face Frame Assembly - Bronze	1
320-019	Glare Shield for FL - Bronze	1
320-022	Wireguard for FL	1

Ordering Format

example: **FL** - **100** **MH** **Q** **PK**

<p>PRODUCT SERIES FL = Small Flood Light</p>	<p>WATTAGE 26 = 26W 32 = 32W 35 = 35W 42 = 42W</p> <p>50 = 50W 70 = 70W 100 = 100W 150 = 150W</p> <p>LAMP TYPE MH = Low Wattage Pulse Start H = High Pressure Sodium FL = Fluorescent</p>	<p>BALLAST VOLTAGE Blank = 120V Q = Quad Volt 4 = 480 Volt U = 120-277* Volt *Fluorescent Only</p> <p>WIRING PC = Button Photocell 120 P2 = Button Photocell 208 P3 = Button Photocell 240 P4 = Button Photocell 277</p>	<p>LAMP OPTION PK = With Lamp Blank = No Lamp</p>
--	---	--	---

MH vs. Fluorescent

	50w MH	42w FL
Lamp Life	5,000 hrs	12,000 hrs
Start Up Time	3-5 minutes	Instant
Restrike Time	15-20 minutes	Instant
CRI	70	82
Color Temperature	4,200k	4,100k
Initial Lumens	3,400	3,200
Mean Lumens	2,700	2,750
Mean Lumens/Watt	39.13	65.52
Watts/Fixture	69	42
Cost/Year*	\$16.12	\$9.81

*Based On: 8 hours per day | 365 days per year | \$0.08 per kWh

