

## LR 110L TB58 J

## Remote Sensors

Standard, Remote Photoelectric Systems

**Compatible Transmitter:**

LT 110L TB58 J



Product Data	
Function:	Receiver
Housing Material:	Nickel Plated Brass
Housing:	M12 x 1
Connection:	4 pin, M12 plug
Sensing Range:	Up to 40 m
Optical Angle:	+/- 3° (opening)
Indicators:	Yes

Technical Data	
Photo Transistor:	Silicon NPN
Power On Indicator:	Green LED
Output Indicator:	-
Light Source:	-
Cable:	-
Housing Material Sensor Housing:	Nickel Plated Brass
Housing Material Lens Cover:	Polycarbonate
Transmitter Diode:	-
Cable Sleeve:	-
Min. Cable Bending Radius:	-

Environmental Data	
Vibration:	10 – 55 Hz, 0,5 mm
Shock:	30 g
Operation Temperature:	- 25 to +65 °C
Storage Temperature:	- 40 to +80 °C
Sealing Class:	IP 67
Light Immunity 20':	> 100 000 lux

Approvals




Connections

4 pin, M12


Sensor Plug  
(Male)




Cable Plug  
(Female)



Wiring Diagram




Dimensions




Sensing Characteristics


Parallel Displacement



Series 110



Angular Displacement



LR 110