



For more Information  
please call

1-800-Belden1



## General Description:

16 AWG triads stranded (7x24) bare copper conductors, twisted triads, overall Beldfoil® shield (100% coverage), PVC/Nylon insulation, PVC jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Triads	AWG	Stranding	Conductor Material
1	16	7x24	BC - Bare Copper

Total Number of Conductors: 3

### Insulation

Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

### Inner Shield

Inner Shield Color Code Chart:

Number	Color
1	Black & White & Red

### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
18	7x26	TC	Tinned Copper

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.047

Outer Jacket Ripcord: Yes

### Overall Cable

Overall Nominal Diameter: 0.310 in.

### Pair

Pair Lay Length & Direction:

Lay Length (in.)	Twists (twist/ft)
2.250	5.330

## Mechanical Characteristics (Overall)

Wet Temperature Range: -30°C To +75°C

Dry Temperature Range: -30°C To +90°C

Bulk Cable Weight: 67 lbs/1000 ft.

Max. Recommended Pulling Tension: 129 lbs.

Min. Bend Radius/Minor Axis: 3.100 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification: NPLF, TC-ER

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	ICEA S-73-532, S-61-402

### Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT4
IEEE Flame Test:	1202

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Electrical Characteristics (Overall)

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.67

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

4.99

#### Max. Operating Voltage - UL:

Voltage

600 V RMS (NEC Type TC)

150 V RMS (NPLF)

### Notes (Overall)

Notes: Alterante color coding available upon request.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3091A 01010000	10,000 FT	720.000 LB	BLACK		3 #16 PVC/NYL FS PVC

Revision Number: 1    Revision Date: 02-13-2014

© 2016 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.