

Download

overlaminates to protect the print. Superior resistance to abrasion, solvents, water, oil and dirt.

Figure 29

Figure 32



Fits Printer Models	Diagram	Part Number	B-#	Material	Color	Approx. Wire Gauge*	Label Width A Inch (mm)	Label Height B Inch (mm)	Print-On Height C Inch (mm)	Labels Per Row
TLS, BMP71*	Fig. 29	PTL-105-427-AW	B-427	Vinyl	White	All White	1.100 (27.9)	0.250 (6.4)	0.250 (6.4)	1
TLS, BMP71*	Fig. 32	PTL-10-427	B-427	Vinyl	White	16 to 10	0.250 (6.4)	0.750 (19.1)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	BM71-11-427	B-427	Vinyl	White	16 to 10	0.500 (12.7)	0.750 (19.1)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-11-427	B-427	Vinyl	White	16 to 10	0.500 (12.7)	0.750 (19.1)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-96-427	B-427	Vinyl	White	16 to 10	1.000 (25.4)	0.750 (19.1)	0.375 (9.5)	1
TLS, BMP71*	Fig. 29	PTL-30-427-AW	B-427	Vinyl	White	All White	1.500 (38.1)	0.750 (19.1)	0.750 (19.1)	1
TLS, BMP71*	Fig. 32	BM71-17-427	B-427	Vinyl	White	12 to 10	0.500 (12.7)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-17-427	B-427	Vinyl	White	12 to 10	0.500 (12.7)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	BM71-18-427	B-427	Vinyl	White	10 to 4	0.750 (19.1)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-18-427	B-427	Vinyl	White	10 to 4	0.750 (19.1)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-19-427	B-427	Vinyl	White	12 to 10	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	BM71-19-427	B-427	Vinyl	White	12 to 10	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-19-642	B-427	Vinyl	White	12 to 10	1.000 (25.4)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-104-427	B-427	Vinyl	White	12 to 10	1.500 (38.1)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-87-427	B-427	Vinyl	White	12 to 10	1.750 (44.5)	1.000 (25.4)	0.375 (9.5)	1
TLS, BMP71*	Fig. 29	PTL-78-427-AW	B-427	Vinyl	White	All White	1.900 (48.3)	1.000 (25.4)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	PTL-102-427	B-427	Vinyl	White	10 to 4	0.500 (12.7)	1.250 (31.8)	0.375 (9.5)	1
TLS, BMP71*	Fig. 32	PTL-103-427	B-427	Vinyl	White	10 to 4	1.000 (25.4)	1.250 (31.8)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-28-427	B-427	Vinyl	White	10 to 4	0.250 (6.4)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	BM71-29-427	B-427	Vinyl	White	10 to 4	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-29-427	B-427	Vinyl	White	10 to 4	0.500 (12.7)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	BM71-30-427	B-427	Vinyl	White	10 to 4	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-30-427	B-427	Vinyl	White	10 to 4	0.750 (19.1)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-31-427	B-427	Vinyl	White	10 to 4	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	BM71-31-427	B-427	Vinyl	White	10 to 4	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-31-642	B-427	Vinyl	White	10 to 4	1.000 (25.4)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	BM71-32-427	B-427	Vinyl	White	10 to 4	1.500 (38.1)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-32-427	B-427	Vinyl	White	10 to 4	1.500 (38.1)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-88-427	B-427	Vinyl	White	10 to 4	1.750 (44.5)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	BM71-107-427	B-427	Vinyl	White	10 to 4	2.000 (50.8)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 32	PTL-107-427	B-427	Vinyl	White	10 to 4	2.000 (50.8)	1.500 (38.1)	0.500 (12.7)	1
TLS, BMP71*	Fig. 27	PTL-74-427	B-427	Vinyl	White	Cables	0.500 (12.7)	2.200 (55.8)	0.750 (19.1)	1
TLS, BMP71*	Fig. 32	PTL-21-427	B-427	Vinyl	White	Cables	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	1
TLS, BMP71*	Fig. 32	BM71-21-427	B-427	Vinyl	White	Cables	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	1
TLS, BMP71*	Fig. 32	PTL-21-642	B-427	Vinyl	White	Cables	1.000 (25.4)	2.500 (63.5)	0.750 (19.1)	1
TLS, BMP71*	Fig. 32	PTL-157-427	B-427	Vinyl	White	Cables	1.500 (38.1)	2.500 (63.5)	0.750 (19.1)	1
TLS, BMP71*	Fig. 42	PTL-75-427	B-427	Vinyl	White	Cables	1.000 (25.4)	2.625 (66.7)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	PTL-66-427	B-427	Vinyl	White	Cables	1.938 (49.2)	3.150 (80.0)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	PTL-77-461	B-427	Vinyl	White	Cables	1.500 (38.1)	3.500 (88.9)	1.250 (31.8)	1
TLS, BMP71*	Fig. 43	PTL-64-427	B-427	Vinyl	White	Cables	1.000 (25.4)	3.375 (85.7)	1.125 (28.6)	1
TLS, BMP71*	Fig. 43	BM71-64-427	B-427	Vinyl	White	Cables	1.000 (25.4)	3.375 (85.7)	1.125 (28.6)	1
TLS, BMP71*	Fig. 32	PTL-23-427	B-427	Vinyl	White	Cables	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	BM71-23-427	B-427	Vinyl	White	Cables	1.000 (25.4)	4.000 (101.6)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	PTL-33-427	B-427	Vinyl	White	Cables	1.500 (38.1)	4.000 (101.6)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	BM71-33-427	B-427	Vinyl	White	Cables	1.500 (38.1)	4.000 (101.6)	1.000 (25.4)	1
TLS, BMP71*	Fig. 32	BM71-109-427	B-427	Vinyl	White	Cables	1.500 (38.1)	4.000 (101.6)	1.500 (38.1)	1
TLS, BMP71*	Fig. 56	PTL-109-427	B-427	Vinyl	White	Cables	1.500 (38.1)	4.000 (101.6)	1.500 (38.1)	1
TLS, BMP71*	Fig. 32	PTL-34-427	B-427	Vinyl	White	Cables	1.500 (38.1)	6.000 (152.4)	1.500 (38.1)	1
TLS, BMP71*	Fig. 32	BM71-34-427	B-427	Vinyl	White	Cables	1.500 (38.1)	6.000 (152.4)	1.500 (38.1)	1

B-427 Self-Laminating Vinyl Labels conti



Finding the correct label height for your Self Laminating labels.

If you know your wire diameter or wire circumference, you can easily determine the correct label height by using the formula below.

Step 1: wire diameter x 3.147 (pi) = wire circumference

Step 2: wire circumference x 1.5 (allowing label to wrap 1.5 times around wire) = total label l

See all TLS2200® and PC Link™ Ribbon parts on page 323.

*Approx. wire gauge based on AW

* Yellow media adaptor required for use in the BMP®71 printer. See page 324.

1-888-272-3946

BradyID.com/s34