



GE
Lighting

62706 - GE energy-efficient halogen 90 watt PAR38 floodlight 1-pack

90PARH1500FL25TP

- ☞ GE energy-efficient halogen bulbs deliver crisp, white light. This unsurpassed light quality is ideal for adding depth, drama and interest to any room or outdoor space. These GE energy-efficient halogen floodlights use less energy than standard halogen bulbs, saving money on energy. GE energy-efficient halogen floodlights feature lenses designed to provide a precise beam pattern, dispensing broad beams of crisp, white light throughout your home. Use these bulbs in indoor track and recessed fixtures or outdoor security fixtures instead of regular incandescent and create a dramatic effect
- ☞ Estimated yearly energy costs \$10.84 based on 3 hours per day \$0.11 per kWh
- ☞ Lasts 1.4 years based on 3 hours per day usage
- ☞ PAR38 indoor/outdoor floodlight with medium base for use in outdoor security lighting and indoor directional fixtures

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Material	Borosilicate glass
Filament	CC-8
Rated Life Hours-nominal	1500 h
Primary Application	Indoor Floodlight
Product Technology	Halogen
Base	E26
Bulb Shape	PAR38

PHOTOMETRIC CHARACTERISTICS

Beam Spread	25 deg
Center Beam Candle Pwr Candela	6850 cd
Nominal Initial Lumen per Watt	20
Initial Lumens-nominal	1790 lm
Color Rendering Index-CRI	100
Color Temperature	2900 K

PRODUCT INFORMATION

Product Code	62706
Description	90PARH1500FL25TP
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168627061
Standard Package GTIN	00043168627061
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168627061
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	4.75 in
----------	---------

ELECTRICAL CHARACTERISTICS

Burn Position	Universal burning position
Input Voltage [nom]	120 V
Rated power (Watts)	90 W