

Ceramalux Non-ALTO

Ceramalux 1000W Mog ED37 CL

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.



Product data

• General Characteristics

Base	Mogul [Mogul]
Base Information	Nic/Brass [Nickel/Brass Base]
Bulb	ED37
Bulb Material	Hard Glass
Bulb Finish	Clear
Operating Position	Universal [Any or Universal (U)]
Main Application	General and Street Lighting
Rated Avg. Life	24000 hr

• Light Technical Characteristics

Color Rendering Index	21 Ra8
Color Temperature	2100 K
Color Temperature technical	2100 K
Initial Lumens	125000 Lm
Luminous Efficacy Lamp	125 Lm/W
Lumen Maintenance EM 10000h	90 %
Photosynthetic Photon Flux PPF	1550 umol/s
Design Mean Lumens	112000 Lm
Chromaticity Coordinate X	517 -
Chromaticity Coordinate Y	423 -

• Electrical Characteristics

Watts	1000 W
Lamp Voltage	225 V
Lamp Current	4.7 A
Ignition Time	5 (max) s

Re-ignition Time [min]	2 (max) min
------------------------	-------------

• Environmental Characteristics

Mercury (Hg) Content	55.2 (max) mg
Picogram per Lumen Hour	20.5 p/LuHr

• Luminaire Design Requirements

Cap-Base Temperature	210 (max) C
Bulb Temperature	400 (max) C

• Product Dimensions

Light Center Length L	7 in
Max Overall Length (MOL) - C	11.5 (max) in
Diameter D	4.625 in

• Footnotes

Footnotes HID	376 [For use in fixtures which do not redirect a substantial portion of the energy toward the arc tube; otherwise very early failure is anticipated. (376)]
---------------	---

• Product Data

Product number	323865
Full product name	Ceramalux 1000W Mog ED37 CL
Short product name	C1000S52/ED37 6PK

PHILIPS

Ceramalux Non-ALTO



Pieces per Sku 1
eop_pck_cfg 6
Skus/Case 6
Bar code on pack 46677323868

Bar code on case 50046677323863
Logistics code(s) 928601140701
eop_net_weight_pp 0.001 kg

Dimensional drawing

Ceramalux 1000W Mog ED37 CL

Product	C (Max)	D (Norm)
HPS R 1000W E39 ED37 U	11.5	4.625



E39



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, June 6
data subject to change