

TAPPAN™



A Southwire Company

100 Bradley Parkway • Blauvelt, NY 10913
Phone: 1-800-WIRE-911 • Fax: 1-845-353-9315

SPECIFICATION SHEET

TAPPAN Spec. F40015.1

Update 1.3 5/10/2012

2C 18 AWG SHIELDED FIRE PROTECTIVE SIGNALING POWER LIMITED CIRCUIT CABLE 75C 300V RISER RATED

CONSTRUCTION: 18 AWG SOLID BARE COPPER 2 CONDUCTORS TWISTED
INSULATION: SR-PVC
COLOR CODE: BLACK, RED
SHIELD/DRAIN: ALUMINUM/POLYESTER FOIL (OUT); 24AWG 7 STRAND TINNED COPPER DRAIN
ASSEMBLY: 2 CONDUCTORS TWISTED, SHIELDED AND JACKETED
JACKET: PVC RED
DIAMETER: 0.147" Nominal
CABLE WT: 18 Lbs/1000Ft Approx (Net Weight)
PRINT LEGEND: E75610 FPLR/CMR/CL3R 18AWG (UL) c(UL) CMG MADE IN USA RoHS COMPLIANT
NEC: FPLR/CMR/CL3R
FOR PLENUM RATED VERSION GO TO SPEC. NO. G40006
COMPLIANCE: UL 1424 FPLR by (UL) / NEC ARTICLE 760 / CSA C22.2 CMG by c(UL) / RoHS
FLAME TEST: UL 1666 Vertical Riser / CSA FT4 (UL 1581)
CAPACITANCE: 49 pF/ft Nominal
VEL OF PROP: 55%
IMPEDANCE: 37 OHMS
RESISTANCE: 6.385 OHMS D.C. PER 1000 FT @ 68 DEG. F Maximum
TEMP/VOLTAGE: 75C / 300V
MISC: MADE IN USA
TAPPAN PART No: 1880BB2M/FPLR/CMR

* +/- 10% Manufacturing tolerance

* On non-standard product, customer agrees to accept all lengths manufactured



Tappan Wire & Cable Inc. provides information and specifications on an "as is" basis. Information in specifications described herein are subject to error and/or omission, and subject to change without notice. Although we make all efforts possible to ensure the accuracy and timeliness of the information, Tappan Wire & Cable, will not be held liable for any damages whatsoever, even if advised of the possibility of such damages, arising from the use, or inability to use, the information or specifications herein. Please refer to our "Website Use Policy", listed on our website, www.tappanwire.com, under the Sales Support Section for full details, or contact your Tappan Representative. This drawing may contain patented or proprietary information. It is the property of Tappan Wire and must not be used in any way detrimental to Tappan Wire. Acceptance by signature of this drawing will be considered as an agreement of and acceptance of the foregoing.