



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192

**PART NUMBER:** 55308  
**DESCRIPTION:** 18/8 SOLID CL2 THERMOSTAT CABLE  
**CONSTRUCTION:** This cable consists of eight bare copper insulated conductors with an overall jacket.  
**APPROVALS:** UL Standard 13, NEC Article 725.  
**APPLICATION:** Class 2 Power Limited Circuit Cable Used In Thermostat Control Applications

## Construction Parameters:

## Cable Cross-Section

Conductor 18 AWG Bare Copper  
Stranding Solid  
Insulation Material Polypropylene  
Insulation Thickness 0.006" Nom.  
Insulated Conductor Diameter 0.052" Nom.  
Number of Conductors 8  
Lay Length Parallel  
Jacket Material PVC  
Jacket Thickness 0.015" Nom.  
Overall Cable Diameter 0.202" Nom.  
Approximate Cable Weight 51.5 Lbs/1M' Nom.  
Flame Rating UL 1581 Vertical Tray Flame Test



## Electrical & Environmental Properties:

Temperature Rating -20°C to 60°C  
Operating Voltage 150V Voltage Rating Per National Electric Code Article 725  
Capacitance Between Conductors @ 1 KHz 25 pF/ft Nom.  
Capacitance Between Conductors to Shield @ 1 KHz -----  
DC Resistance per Conductor @ 20°C 6.32 Ohms/1M' Nom.

Insulation Colors Red White Green Blue Yellow Brown Orange Black  
Jacket Color Brown (Other colors available for minimum order)  
Legend (Surface Ink Print) TYPE CL2 C(ETL)US (ETL CODE) 18 AWG 8/C BAROSTAT II SUN RES -- CMX  
OUTDOOR -- TYPE CMH FT1 XX/XX/XX (MONTH/DAY/YEAR) XXXXXX (W/O #)

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

Cable has a rip cord for easy jacket removal

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_

Customer Approval \_\_\_\_\_

Specification Issue Date: March 25, 2009

# Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

\* Not all options are available for each product



## Coleman Cable Part Legend



Put-ups	Code	Colors	Code		Code
Reel, 250 ft	04	White	01	Pink	11
Reel, 500 ft	05	Yellow	02	Purple	13
Reel, 1,000 ft	06	Orange	03	Clear	18
Reel-in-box, 1,000 ft	16	Red	04	Fluorescent	
RabbitPull™ Pull-Box, 500 ft	45	Green	05	Pink	21
RabbitPull™ Pull-Box, 1,000 ft	46	Blue	06	Ivory	22
SignaCoil™ 500 ft	55	Brown	07	Natural	23
SignaCoil™ 1,000 ft	56	Black	08	Beige	33
		Gray	09	Red Striped	
				CorraClad™	44

