



PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive
Waukegan, IL 60085
Toll-Free (800) 323-9355
Fax: (847) 689-1192

PART NUMBER: 55502
DESCRIPTION: 18/2 SOLID CMP/CL2P FT6 THERMOSTAT CABLE
CONSTRUCTION: This cable consists of two bare copper insulated conductors with an overall jacket.
APPROVALS: UL Standard 13 and 444, NEC Articles 725 and 800.
APPLICATION: Class 2 Power Limited Circuit Cable And Communications Used In Plenum Thermostat Control Applications

Construction Parameters:

Cable Cross-Section

Conductor 18 AWG Bare Copper
Stranding Solid
Insulation Material Low Smoke PVC
Insulation Thickness 0.006" Nom.
Insulated Conductor Diameter 0.052" Nom.
Number of Conductors 2
Lay Length Parallel
Jacket Material Low Smoke PVC
Jacket Thickness 0.014" Nom.
Overall Cable Diameter 0.133" Nom.
Approximate Cable Weight 17.0 Lbs/1M' Nom.
Flame Rating CSA FT6/NFPA 262 Steiner Tunnel Smoke and Flame Test



Electrical & Environmental Properties:

Temperature Rating -20°C to 75°C
Operating Voltage 300V RMS Max.
Capacitance Between Conductors @ 1 KHz 51 pF/ft Nom.
Capacitance Between Conductors to Shield @ 1 KHz -----
DC Resistance per Conductor @ 20°C 6.32 Ohms/1M' Nom.

Insulation Colors Black Red
Jacket Color Beige (Other colors available for minimum order)

Legend (Surface Ink Print) BARON WIRE 55502 18 AWG 2/C C(ETL)US (ETL CODE) TYPE
CMP/CL2P 75C BAROPLEN -- TYPE CMP FT6

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

Cable has a rip cord for easy jacket removal

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name _____

Customer Approval _____

Specification Issue Date: January 26, 2007