



# PRODUCT DATA SHEET

Controlled Document - Engineering Drive


1530 Shields Drive  
Waukegan, IL 60085  
Toll-Free (800) 323-9355  
Fax: (847) 689-1192

**PART NUMBER:** 55504  
**DESCRIPTION:** 18/4 SOLID CMP/CL2P FT6 THERMOSTAT CABLE  
**CONSTRUCTION:** This cable consists of four bare copper insulated conductors with an overall jacket.  
**APPROVALS:** UL Standard 13 and 444, NEC Articles 725 and 800.  
**APPLICATION:** Class 2 Power Limited Circuit Cable And Communications Used In Plenum Thermostat Control Applications

## Construction Parameters:

## Cable Cross-Section

Conductor 18 AWG Bare Copper  
Stranding Solid  
Insulation Material PVC  
Insulation Thickness 0.006" Nom.  
Insulated Conductor Diameter 0.052" Nom.  
Number of Conductors 4  
Lay Length Parallel  
Jacket Material PVC  
Jacket Thickness 0.014" Nom.  
Overall Cable Diameter 0.155" Nom.  
Approximate Cable Weight 29.1 Lbs/1M' Nom.  
Flame Rating CSA FT6/NFPA 262 Steiner Tunnel Smoke and Flame Test



## Electrical & Environmental Properties:

Temperature Rating -20°C to 75°C  
Operating Voltage 300V RMS Max.  
Capacitance Between Conductors @ 1 KHz 48 pF/ft Nom.  
Capacitance Between Conductors to Shield @ 1 KHz -----  
DC Resistance per Conductor @ 20°C 6.32 Ohms/1M' Nom.

Insulation Colors Black Red White Green  
Jacket Color Beige (Other colors available for minimum order)

Legend (Surface Ink Print) BARON WIRE 55504 18 AWG 4/C C(ETL)US (ETL CODE) TYPE  
CMP/CL2P 75C BAROPLN -- TYPE CMP FT6

This product complies with European Directive 2002/95/EC (RoHS)

On special orders, the customer will accept all factory lengths and +/- 10 percent of total order requested.

Cable has a rip cord for easy jacket removal

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman Cable disclaims all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable.

Customer Name \_\_\_\_\_

Customer Approval \_\_\_\_\_

Specification Issue Date: January 26, 2007