

# Single Meter Sockets Without Bypass

## 200 Amp Self-Contained

Single Meter Sockets/  
Without Bypass

1



204

### APPLICATION

- Single meter position
- Designed to receive watt-hour meters that meet ANSI C12.10
- Surface or semi-flush mounting
- Overhead or underground feed

### CONSTRUCTION

- Type 3R construction
- Some styles available in stainless steel (SS)
- Snap type sealing ring included
- 5th jaw provision at nine o'clock
- Ring style

### STANDARDS

- UL 414 listed, complies with ANSI C12.7

### FINISH

- ANSI 61 gray acrylic electrocoat finish

### ACCESSORIES

- 5th jaw kit — catalog #50365
- Screw type sealing ring — catalog #25016D (included with MS73 catalog numbers)
- Steel and clear lexan covers for socket opening
- AW hubs

### Overhead-Surface Mount

| CATALOG NUMBER | AIC RATING | AMPACITY MAX. | CONT. | VOLTAGE | SERVICE TYPE | NUMBER OF JAWS | HUB PROV. | CONDUCTOR LUG RANGE       |                   | FIGURE NUMBER | DIMENSIONS (INCHES) |           |           |
|----------------|------------|---------------|-------|---------|--------------|----------------|-----------|---------------------------|-------------------|---------------|---------------------|-----------|-----------|
|                |            |               |       |         |              |                |           | PHASE CONDUCTOR LINE/LOAD | NEUTRAL CONDUCTOR |               | HEIGHT (H)          | WIDTH (W) | DEPTH (D) |
| 204            | †          | 200           | --    | 600     | 1Ø 3W        | 4              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 7        | 15                  | 8 ¼       | 4 ⅝       |
| 204MS68*       | †          | 200           | --    | 600     | 1Ø 3W        | 4              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 7        | 15                  | 8 ¼       | 4 ⅝       |
| 204MS68A**     | †          | 200           | --    | 600     | 1Ø 3W        | 4              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 7        | 15                  | 8 ¼       | 4 ⅝       |

\*2" hub included    \*\*Includes 2" hub and screw type sealing ring

### Overhead-Flush Mount

| CATALOG NUMBER | AIC RATING | AMPACITY MAX. | CONT. | VOLTAGE | SERVICE TYPE | NUMBER OF JAWS | HUB PROV. | CONDUCTOR LUG RANGE       |                   | FIGURE NUMBER | DIMENSIONS (INCHES) |           |           |
|----------------|------------|---------------|-------|---------|--------------|----------------|-----------|---------------------------|-------------------|---------------|---------------------|-----------|-----------|
|                |            |               |       |         |              |                |           | PHASE CONDUCTOR LINE/LOAD | NEUTRAL CONDUCTOR |               | HEIGHT (H)          | WIDTH (W) | DEPTH (D) |
| 204F           | †          | 200           | --    | 600     | 1Ø 3W        | 4              | NONE      | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 1,8      | 15                  | 8         | 6         |
| 204FMS73       | †          | 200           | --    | 600     | 1Ø 3W        | 4              | NONE      | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 1,8      | 15                  | 8         | 6         |

### Underground-Surface Mount

| CATALOG NUMBER | AIC RATING | AMPACITY MAX. | CONT. | VOLTAGE | SERVICE TYPE | NUMBER OF JAWS | HUB PROV. | CONDUCTOR LUG RANGE       |                   | FIGURE NUMBER | DIMENSIONS (INCHES) |           |           |
|----------------|------------|---------------|-------|---------|--------------|----------------|-----------|---------------------------|-------------------|---------------|---------------------|-----------|-----------|
|                |            |               |       |         |              |                |           | PHASE CONDUCTOR LINE/LOAD | NEUTRAL CONDUCTOR |               | HEIGHT (H)          | WIDTH (W) | DEPTH (D) |
| U204           | †          | 200           | --    | 600     | 1Ø 3W        | 4              | NONE      | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 2        | 15                  | 12        | 4 ⅝       |
| U204MS73       | †          | 200           | --    | 600     | 1Ø 3W        | 4              | NONE      | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 2        | 15                  | 12        | 4 ⅝       |
| U204MSCD       | †          | 250           | 200   | 600     | 1Ø 3W        | 4              | NONE      | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 2        | 15                  | 12        | 4 ⅝       |
| U204MS73CD     | †          | 250           | 200   | 600     | 1Ø 3W        | 4              | NONE      | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 2        | 15                  | 12        | 4 ⅝       |

### Overhead/Underground-Surface Mount

| CATALOG NUMBER | AIC RATING | AMPACITY MAX. | CONT. | VOLTAGE | SERVICE TYPE | NUMBER OF JAWS | HUB PROV. | CONDUCTOR LUG RANGE       |                   | FIGURE NUMBER | DIMENSIONS (INCHES) |           |           |
|----------------|------------|---------------|-------|---------|--------------|----------------|-----------|---------------------------|-------------------|---------------|---------------------|-----------|-----------|
|                |            |               |       |         |              |                |           | PHASE CONDUCTOR LINE/LOAD | NEUTRAL CONDUCTOR |               | HEIGHT (H)          | WIDTH (W) | DEPTH (D) |
| U204MS21       | †          | 200           | --    | 600     | 1Ø 3W        | 4              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 4        | 15                  | 12        | 4 ⅝       |
| U204SSMS21     | †          | 200           | --    | 600     | 1Ø 3W        | 4              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 4        | 15                  | 12        | 4 ⅝       |
| U207           | †          | 250           | 200   | 600     | 3Ø 4W        | 7              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 6        | 18                  | 12        | 5         |
| U207MS73       | †          | 250           | 200   | 600     | 3Ø 4W        | 7              | AW        | 6 AWG - 250 kcmil         | 6 AWG - 250 kcmil | Fig. 6        | 18                  | 12        | 5         |

MS21 = 2" AW Hub installed