



PRODUCT DATA SHEET

1530 Shields Drive
Waukegan, IL 60085
Toll-Free (800) 323-9355
Fax: (847) 689-1192

PART NUMBER: 76214
DESCRIPTION: 24 AWG /4 Pair PLENUM CATEGORY 3 DATA CABLE *Plen-Lan 3*
RATING: UL Standard 444, ICEA S-80-576, EIA/TIA 568, FT6
CERTIFICATIONS: ETL Listed CMP ETL Verified
Category 3

Construction Parameters:

	<u>INFORMATION</u>	<u>DIAMETER*</u>
Conductors:	Solid Copper	0.020
Dielectric:	Solid LOW SMOKE PVC	0.035
Pair lays:	Each pair has different lay length for cross-talk prevention	-
Ripcord:	Polyester	-
Jacket:	LOW SMOKE PVC	0.160

Electrical Properties:

DC Resistance Max.(ohms/100m @ 20° C):	9.38
DC Resistance Unbalance Max.(%):	5
Characteristic Impedance (ohms): 1-16 MHz	85-115
Pair-to-Ground Cap. Unbal. Max.(pF/100m):	330
Worst-Pair Near-End	772 kHz 43**
Crosstalk Min. (dB):	1.0 MHz 41**
	4.0 MHz 32**
	8.0 MHz 27**
	10.0 MHz 26**
	16.0 MHz 23**

The (**) values are for information only. The min. NEXT coupling loss for any pair combination at room temp. is to be greater than the value determined using the formula $NEXT(F_{MHz}) \geq NEXT(0.772) - 15 \log_{10}(F_{MHz}/0.772)$ for all freq. in the range of 772 MHz-16 MHz for a min. length of 100 m.

Attenuation Max.(db/100m):	256 kHz	1.3
	512 kHz	1.8
	772 kHz	2.2*
	1.0 MHz	2.6*
	4.0 MHz	5.6*
	8.0 MHz	8.5*
	10.0 MHz	9.7*
	16.0 MHz	13.1*

The asterisk (*) values are for information only. The maximum loss for any pair at room temp. is to be determined using the formula $Att(f) \leq 2.32[SQR(f)] + 0.238(f)$

Structural Return	1.0- 10.0 MHz	12
Loss Min. (dB):	16.0 MHz	10**

The (**) values are for information only. The SRL is to be determined using the formula $SRL_F \geq SRL_{10} - 10 \log_{10}(F/10)$

Miscellaneous Information:

Pair Colors: W/Bl with Bl/W, W/Or with Or/W, W/Gn with Gn/W, W/Bn with Bn/W
Jacket Color: NATURAL
Jacket Print: CAT3 COLEMAN CABLE 76214 CAT3 24 AWG C(ETL)US LISTED 2003548
TYPE CMP ETL VERIFIED TO TIA/EIA-568-B.2 CAT3 FT6 DATE CODE
REEL# SEQ FTG CAT3 (EVERY FOOT)
(Also printed with sequential footage, date code and reel #)
Flame rating: NFPA 262 Steiner Tunnel Smoke and Flame Test
Applicable NEC Article: 800
Applicable TIA/EIA: 568-B.2
Approximate Weight (lb/1000 ft): 18

This product complies with European Directive 2002/95/EC (RoHS)

On special orders the customer will accept all factory lengths and $\pm 10\%$ of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Coleman Cable's control, all product data presented is for informational purposes only and does not create a binding obligation or liability on Coleman Cable or confer any rights on any customer. The sale of product (s) is conditioned upon acceptance of a purchase order subject to Coleman Cable's standard terms and conditions contained therein, including without limitation Coleman Cable's standard warranty. Coleman cable disclaims all liability in connection with the use of information contained herein or otherwise.

Company Name: _____

Customer Approval: _____

Date: _____