

## 5 x 20mm European (IEC) Ferrule Fuses

### S506-V (GDC-V)\* (axial leads)

### S506 (GDC)\*

#### Specifications

**Description:** Time-delay, low-breaking capacity fuse.

**Construction:** Glass tube, nickel-plated brass endcaps.

#### Ratings:

Volts — 250Vac (or less)

Amps — 32mA-15A\*\*

IR — 35A @ 250Vac



**Agency Information:** UR, CSA, cURus, SEMKO, VDE, BSI, IMQ, PSE/JET, CCC.

See data sheet for complete agency information. Not all approvals apply to all ratings.

#### Features and Benefits

- Time-delay compatibility for inductive circuits.
- Conforming to IEC standards.

#### Typical Applications

- Electronic Circuits

#### Catalog Numbers (Amps)

Catalog Numbers	Typical $I^2t$	Max Voltage Drop (mV)
S506-32-R	0.0051	1050
S506-40-R	0.0072	920
S506-50-R	0.0095	800
S506-63-R	0.021	760
S506-80-R	0.038	580
S506-100-R	0.045	490
S506-125-R	0.063	390
S506-160-R	0.093	320
S506-200-R	0.114	340
S506-250-R	0.265	270
S506-315-R	0.621	250
S506-400-R	0.872	210
S506-500-R	0.827	140
S506-630-R	1.33	150
S506-800-R	2.78	75
S506-1-R	6.45	87.5
S506-1.25-R	10.05	86
S506-1.6-R	21.7	82
S506-2-R	31.6	77
S506-2.5-R	59.4	72.5
S506-3.15-R	96.4	68.5
S506-4-R	71.8	67
S506-5-R	142.5	60.5
S506-6.3-R	237.6	54
S506-8-R	255.8	55
S506-10-R	450	54
S506-12.5-R	1019.5	45
S506-15-R	1091.7	65.5

#### Options

Axial leads, put "V" in P/N.

\*When ordering GDC version, do not add "-R" suffix to part number.

\*\*GDC series is not available above 6.3A.

**Data Sheet: 2016 (GDC), 4332 (S506)**