

UL 98 Non-Fused Rotary Disconnect Switches—100, 200 and 400A

For a Complete Assembly, Please Select:

Switch + Lugs		Switch								
		Switch Amp Rating	No. of Poles	SCCR	Max Horsepower Rating				Part Number	
					1-Phase 220/240Vac	220/240Vac	3-Phase 440/480Vac	600 Vac		
		100	3	200kA	10	30	75	100	RD100-3-SCCR	
		200	3	200kA	10	75	150	200	RD200-3	
		200	4	200kA	10	75	150	200	RD200-4	
		400	3	200kA	-	125	250	350	RD400-3	
		400	4	200kA	-	125	250	350	RD400-4	
		Terminal Lug Kit								
		Switch Amp Rating	No. of Poles	Lugs Per Kit	Wire Range		Wire Type	Part Number		
		100-200	2	2	#6-300MCM		75°C Cu/Al	LUG1-2		
		100-200	3	3	#6-300MCM		75°C Cu/Al	LUG1-3		
100-200	4	4	#6-300MCM		75°C Cu/Al	LUG1-4				
400	2	2	#4-600MCM or Dual 1/0-250MCM		75°C Cu/Al	LUG2-2				
400	3	3	#4-600MCM or Dual 1/0-250MCM		75°C Cu/Al	LUG2-3				
400	4	4	#4-600MCM or Dual 1/0-250MCM		75°C Cu/Al	LUG2-4				
400	2	2	(2) #6-350MCM		75°C Cu/Al	LUG3-2				
400	3	3	(2) #6-350MCM		75°C Cu/Al	LUG3-3				
400	4	4	(2) #6-350MCM		75°C Cu/Al	LUG3-4				
Select for Standard Applications		Direct Mount Handle - mounts directly to switch, no shaft required								
		For Switch Part Number	Color	Test Function	Padlockable			Part Number		
	All Switches	Black	N	Y			DIR-03			
	OR									
	HANDLE		External Front Operated Pistol Handles - shaft required							
			NEMA Type	Color	Test Function	Padlockable	Defeatable	Part Number		
			1, 3R, 12	Black	N	Y	Y	H12-03B		
			1, 3R, 12	Red/Yellow	N	Y	Y	H12-03R		
			1, 3R, 4, 4X, 12	Black	N	Y	Y	H4X-06B		
			1, 3R, 4, 4X, 12	Red/Yellow	N	Y	Y	H4X-06R		
			Metalic Hasp (Heavy Duty) External Front Operated Pistol Handles - shaft required							
			NEMA Type	Color	Test Function	Padlockable	Defeatable	Part Number		
1, 3R, 4, 4X, 12			Black	N	Y	Y	H4X-06BHD			
1, 3R, 4, 4X, 12			Red/Yellow	N	Y	Y	H4X-06RHD			
Shafts for Pistol Handles										
Length in (mm)			Mounting Depth (X) in (mm)					Part Number		
7.9 (200)	5.31~10.43 (135~265)					SH5-200				
12.6 (320)	5.31~15.16 (135~385)					SH5-320				
15.7 (400)	5.31~18.31 (135~465)					SH5-400				
Shaft Guide							Part Number			
Required for 15.7" (400mm) long shafts, optional for other lengths							SH-GUIDE2			
and ...										
Accessories		Auxiliary Contacts								
		Contact Type	Number of Contacts	Continuous Amp Rating	Voltage Rating	Max Number of Aux Contacts per Switch	Part Number			
		NO + NC	1 of each	10.1A	125-250Vac	2	BAC03*			
		NO + NC	1 of each	10.1A	125-250Vac	2	BAC04*			
		NO + NC	1 of each	1A	125Vac	2	BAC11*			
		NO + NC	1 of each	1A	125Vac	2	BAC12*			
		* For one auxiliary contact, install either BAC03 or BAC11. For two auxiliary contacts, install BAC03 + BAC04, or BAC11 + BAC12.								