

**North American Standards -  
General Purpose**

**Gland Type:**


Non-armoured

**Cable Type:**

Non-armoured and tray cable

**Certifications and Compliances:**

- cULus Listed - UL File E23223
- Suitable for use in Class I, Div. 2 hazardous locations when installed in accordance with NEC501.10(B)(2)



4F

**Features:**

- Form A - D bodies and gland nuts – steel with zinc electroplate and chromate finish coat
- Form E - F bodies and gland nuts – Feraloy® iron alloy with electrogalvanized and aluminum acrylic paint
- Weatherproof seal on outer sheath of cable
- Standard neoprene seal suitable for use in operating temperatures -25° to 40°C
- Available with NPT threads
- Available in all aluminum construction
- See page 102 for related accessories

**ORDERING EXAMPLE:**

CGB192 -SG	
Gland Type	Options

**OPTIONS (add after gland type):**

- SG Sealing Gasket\* – only applies to certain sizes (e.g., CGB192-SG)
- SA Aluminum Construction† – only applies to certain sizes (e.g., CGB114-SA)

**SELECTION TABLE**

Entry Thread Size 'A'		Form	Thread Length 'B' NPT	Cable Acceptance		Gland Length 'F' (less entry)	External Diameter 'G'	Hexagon Dimensions	
NPT Size	NPT Catalog #			Outer Sheath 'E'				Across Flats	Across Corners 'G'
				Min	Max				
3/8"	CGB3814	A	0.438	0.125	0.250	1.063	-	0.750	0.875
3/8"	CGB3816	A	0.438	0.250	0.375	1.063	-	0.750	0.875
3/8"	CGB3817	A	0.438	0.375	0.437	1.063	-	0.750	0.875
3/8"	CGB3892	B	0.438	0.125	0.250	1.313	-	1.000	1.188
3/8"	CGB3893	B	0.438	0.250	0.375	1.313	-	1.000	1.188
3/8"	CGB3894	B	0.438	0.375	0.500	1.313	-	1.000	1.188
1/2"	CGB114†	A	0.625†	0.125	0.250	1.000	-	0.875	1.188
1/2"	CGB116†	A	0.625†	0.250	0.375	1.000	-	0.875	1.188
1/2"	CGB117†	A	0.625†	0.375	0.437	1.000	-	0.875	1.188
1/2"	CGB192*†	B	0.750*†	0.125	0.250	1.313	-	1.000	1.188
1/2"	CGB193*†	B	0.750*†	0.250	0.375	1.313	-	1.000	1.188
1/2"	CGB194*†	B	0.750*†	0.375	0.500	1.313	-	1.000	1.188
1/2"	CGB195*†	B	0.750*†	0.500	0.625	1.313	-	1.000	1.188
1/2"	CGB196*	C	0.625*	0.625	0.750	1.750	-	1.500	1.656
1/2"	CGB197*†	C	0.625*†	0.750	0.875	1.750	-	1.500	1.656
3/4"	CGB292†	B	0.625†	0.125	0.250	1.375	-	1.060	1.250
3/4"	CGB293†	B	0.625†	0.250	0.375	1.375	-	1.060	1.250
3/4"	CGB294†	B	0.625†	0.375	0.500	1.375	-	1.060	1.250
3/4"	CGB295†	B	0.625†	0.500	0.625	1.375	-	1.060	1.250
3/4"	CGB296*†	C	0.625*†	0.625	0.750	1.750	-	1.630	1.656
3/4"	CGB297*†	C	0.625*†	0.750	0.875	1.750	-	1.630	1.656
3/4"	CGB298*†	D	0.625*†	0.875	1.000	2.500	2.250	-	-
1"	CGB393†	B	0.688†	0.250	0.375	1.375	-	1.375	1.625
1"	CGB394†	B	0.688†	0.375	0.500	1.375	-	1.375	1.625
1"	CGB395*†	C	0.688*†	0.500	0.625	1.688	-	1.500	1.875
1"	CGB396*†	C	0.688*†	0.625	0.750	1.688	-	1.500	1.875
1"	CGB397*†	C	0.688*†	0.750	0.875	1.688	-	1.500	1.875
1"	CGB3239†	C	0.688†	0.875	1.000	1.688	-	-	1.875
1"	CGB398*†	D	0.625*†	0.875	1.000	2.375	2.375	-	-
1"	CGB399*†	D	0.625*†	1.000	1.188	2.375	2.375	-	-
1"	CGB3911*†	D	0.625*†	1.188	1.375	2.375	2.375	-	-

All dimensions in inches unless otherwise noted.

\*With optional Sealing Gasket.

†With optional Aluminum Construction.