

# Ordering Information



TP548



TP549



TP523



TP563



TP554  
TP842



TP556  
TP832



TP558  
TP835



TP560  
TP836



TP562



TP557



TP521

## 4<sup>11</sup>/<sub>16</sub>" Steel Outlet Boxes

Catalog No.	Description	Depth	Knockouts		Cubic In. Capacity	Std. Unit Pkg.	Wt. Lbs. Per 100
			Sides	Bottom			
TP548	Drawn	1½"	8 – ½", 4 – ¾"	3 – ½", 2 – ¾"	29.5	25	84
TP549	Drawn	1½"	6 – ½", 6 – ½" & ¾" C	3 – ½", 2 – ¾"	29.5	25	84
TP523	Welded	1½"	12 – ½" & ¾" C	2 – ½", 2 – ¾"	29.5	25	99
TP563	Drawn	2 <sup>1</sup> / <sub>8</sub> "	6 – ½", 6 – ½" & ¾" C	3 – ½", 2 – ¾"	42.0	25	104
TP554	Drawn	2 <sup>1</sup> / <sub>8</sub> "	8 – ¾"	3 – ½", 2 – ¾"	42.0	25	104
TP556	Drawn	2 <sup>1</sup> / <sub>8</sub> "	8 – ½", 4 – ¾"	3 – ½", 2 – ¾"	42.0	25	104
TP558	Drawn	2 <sup>1</sup> / <sub>8</sub> "	4 – ¾", 4 – 1"	3 – ½", 2 – ¾"	42.0	25	104
TP560	Drawn	2 <sup>1</sup> / <sub>8</sub> "	8 – 1"	3 – ½", 2 – ¾"	42.0	25	104
TP562	Drawn	2 <sup>1</sup> / <sub>8</sub> "	4 – 1¼", VS Bracket	3 – ½", 2 – ¾"	42.0	25	104
TP557	Drawn	2 <sup>1</sup> / <sub>8</sub> "	4 – ½", 5 – ½" & ¾" C	3 – ½", 2 – ¾"	42.0	25	120
TP521	Welded	2 <sup>1</sup> / <sub>8</sub> "	12 – ½" & ¾" C	2 – ½", 2 – ¾"	44.0	25	115

## 4<sup>11</sup>/<sub>16</sub>" Air Plenum\* — For applications where air-tight enclosures are required, use with gasketed air plenum

Catalog No.	Description	Depth	Knockouts		Cubic In. Capacity	Std. Unit Pkg.	Wt. Lbs. Per 100
			Sides	Bottom			
TP835	Drawn	2 <sup>1</sup> / <sub>8</sub> "	4 – ¾", 4 – 1"	3 – ½", 2 – ¾"	42.0	25	115
TP836	Drawn	2 <sup>1</sup> / <sub>8</sub> "	8 – 1"	3 – ½", 2 – ¾"	42.0	25	115
TP842	Drawn	2 <sup>1</sup> / <sub>8</sub> "	12 – ¾"	3 – ½", 2 – ¾"	42.0	25	115
TP832	Drawn	2 <sup>1</sup> / <sub>8</sub> "	8 – ½", 4 – ¾"	3 – ½", 2 – ¾"	42.0	25	115

\* For air plenum (No mounting holes)