

Speed D Feed Bits PC 6355



- Fast Heavy Duty Power Boring
- Tapered Back For Easy Back Out
- Universal 7/16" Shank, 5" OA Length
- Replaceable Double Ended Self Feeding Point

- Open Design For No Clog Fast Chip Removal
- Precision Angled Surface For Smoother Cuts
- Caution! Always Wear Eye Protection

Speed D Feed multi-spur wood boring bits are ideal for boring large holes quickly - from 1" through 4-5/8". This bit is especially suited to electricians and plumbers.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
SDF100	21900	1"	1	6	0.438#	Ea
SDF118	21901	1-1/8"	1	6	0.469#	Ea
SDF114	21902	1-1/4"	1	6	0.500#	Ea
SDF138	21903	1-3/8"	1	6	0.500#	Ea
SDF112	21904	1-1/2"	1	6	0.563#	Ea
SDF134	21905	1-3/4"	1	6	0.625#	Ea
SDF200	21906	2"	1	6	0.719#	Ea
SDF218	21907	2-1/8"	1	6	0.813#	Ea
SDF214	21908	2-1/4"	1	6	0.938#	Ea
SDF2916	21909	2-9/16"	1	6	1.063#	Ea
SDF300	21910	3"	1	6	1.500#	Ea
SDF358	21911	3-5/8"	1	6	2.000#	Ea
SDF458	21912	4-5/8"	1	6	3.500#	Ea

Replacement Screw Points

SDF14S	21913	1/4 x 2-1/2" (For 1" thru 2-9/16")	1	6	0.01#	Ea
SDF14L	21914	1/4 x 2-3/4" (For 3" thru 4-5/8")	1	6	0.01#	Ea

Flex-A-Bit PC 6360



- Self Feeding Point
- Flexible Spring Steel Shaft
- Display Pack
- Caution! Always Wear Eye Protection

Flex A Bits are used to drill within walls and are able to reach normally inaccessible areas through a small opening. After (drilling) through a stud or header, a wire is attached to the fish hole in the flute and the drill is retracted pulling the wire through. The FG357 Flex A Guide tool aids in positioning the bit.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
FB3854	37000	3/8 x 54"	1	6	0.500#	Ea
FB3872	37005	3/8 x 72"	1	6	0.640#	Ea
FB5054	37010	1/2 x 54"	1	6	0.530#	Ea
FB5072	37015	1/2 x 72"	1	6	0.680#	Ea
FB9654	37030	9/16 x 54"	1	6	0.540#	Ea
FB9672	37035	9/16 x 72"	1	6	0.680#	Ea
FB7554	37020	3/4 x 54"	1	6	0.950#	Ea
FB7572	37025	3/4 x 72"	1	6	1.220#	Ea

Flex-A-Bit Tool

FG357	37040	All	1	6	0.450#	Ea
-------	-------	-----	---	---	--------	----



Pilot Drills & Accessories PC 6390



- 1/4" High Speed Drill Pilot
- Split Point Design
- Caution! Always Wear Eye Protection

Pilot drills are available with three flats or three notches. Set screws secure drill in arbor.

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
VPD4	28540	4-1/2 x 1/4" Pilot Drill, Shank Ground 3 Sides	1	10	0.050#	Ea
VPD4N	28545	4-1/2 x 1/4" Pilot Drill, 3 Notches for Set Screw	1	10	0.050#	Ea
VPD4S	28550	3-1/16" Pilot Drill for V24K, V34, & V35P Arbors	1	10	0.050#	Ea
VE121	28555	12" Extension for 7/16" Arbors	1	1	0.800#	Ea
V44N	28560	Adapter Nut- Adapts Arbor with 1/2-20 threads to fit Hole Saw with 5/8-18 Threads	1	1	0.650#	Ea

See new products at Ihdottie.com

Dottie





Hole Saws PC 6380

Variable pitch hole saws are bi-metal construction with an M3 HSS cutting edge which is laser welded to a spring steel back. They will cut to depths of 1-3/8" and will outlast carbon steel hole saws, while the tooth design resists shock and strippage. The saws accept standard arbors and will cut stainless steel, iron, pipe, wood and plastic.

- Bi Metal
- M3 Steel RC65-66
- Shatterproof
- 4/6 Variable Pitch
- Powder Coated
- Accepts Standard Arbors
- Caution! Always Wear Eye Protection

CAT NO	UPC	DIAMETER	USE ARBOR	PIPE SIZE				WT/STD	UNIT
				TAP	ENTR.	STD	MSTR		
VP09	28400	9/16"	V24K, V34, V44			1	10	0.080#	Ea
VP10	28402	5/8"	V24K, V34, V44			1	10	0.090#	Ea
VP11	28404	11/16"	V24K, V34, V44			1	10	0.090#	Ea
VP12	28406	3/4"	V24K, V34, V44		3/8"	1	10	0.090#	Ea
VP13	28408	13/16"	V24K, V34, V44			1	10	0.110#	Ea
VP14	28410	7/8"	V24K, V34, V44	3/4"	1/2"	1	10	0.110#	Ea
VP15	28412	15/16"	V24K, V34, V44			1	10	0.130#	Ea
VP16	28414	1"	V24K, V34, V44			1	10	0.140#	Ea
VP18	28416	1-1/8"	V24K, V34, V44	1"	3/4"	1	10	0.190#	Ea
VP19	28418	1-3/16"	V24K, V34, V44			1	10	0.200#	Ea
VP20	28420	1-1/4"	V35P, V45P			1	10	0.200#	Ea
VP21	28422	1-5/16"	V35P, V45P			1	10	0.210#	Ea
VP22	28424	1-3/8"	V35P, V45P		1"	1	10	0.240#	Ea
VP24	28426	1-1/2"	V35P, V45P			1	10	0.280#	Ea
VP26	28428	1-5/8"	V35P, V45P			1	10	0.340#	Ea
VP28	28430	1-3/4"	V35P, V45P	1-1/2"	1-1/4"	1	10	0.230#	Ea
VP30	28432	1-7/8"	V35P, V45P			1	10	0.270#	Ea
VP32	28434	2"	V35P, V45P		1-1/2"	1	10	0.290#	Ea
VP34	28436	2-1/8"	V35P, V45P			1	10	0.330#	Ea
VP36	28438	2-1/4"	V35P, V45P	2"		1	10	0.360#	Ea
VP37	28440	2-5/16"	V35P, V45P			1	10	0.330#	Ea
VP38	28442	2-3/8"	V35P, V45P			1	10	0.330#	Ea
VP40	28444	2-1/2"	V45P		2"	1	10	0.450#	Ea
VP41	28446	2-9/16"	V45P			1	10	0.450#	Ea
VP48	28448	3"	V45P		2-1/2"	1	10	0.600#	Ea
VP56	28450	3-1/2"	V45P			1	10	0.620#	Ea
VP58	28452	3-5/8"	V45P		3"	1	10	0.660#	Ea
VP64	28454	4"	V45P			1	10	0.810#	Ea
VP66	28456	4-1/8"	V45P		3-1/2"	1	10	0.850#	Ea
VP70	28458	4-3/8"	V45P			1	10	0.910#	Ea
VP72	28460	4-1/2"	V45P			1	10	0.960#	Ea
VP76	28462	4-3/4"	V45P		4"	1	10	1.030#	Ea
VP80	28464	5"	V45P			1	10	1.140#	Ea
VP88	28466	5-1/2"	V45P			1	10	1.300#	Ea
VP96	28468	6"	V45P			1	10	1.530#	Ea



Arbors PC 6390

Arbors are supplied with pilot drills. Check Hole Saw to determine proper arbor.

- Interchangeable With Other Brands
- Includes Replaceable High Speed Pilot Drill
- Caution! Always Wear Eye Protection

CAT NO	UPC	SHANK	THREAD SIZE	DRILL SIZE	DRILL NUMBER	SIZE	CHUCK FITS	STD	MSTR	WT/STD	UNIT
V24K	28500	1/4" Round	1/2-20	1/4"	VPD4	1/4"	9/16" - 1-1/8"	1	1	0.130#	Ea
V34	28505	3/8" Hex	1/2-20	1/4"	VDP4S	3/8"	9/16" - 1-1/8"	1	1	0.150#	Ea
V35P	28510	3/8" Hex	5/8-18	1/4"	VPD4S	3/8"	1-1/4" - 6"	1	1	0.360#	Ea
V44	28515	7/16" Hex	1/2-20	1/4"	VPD4	1/2"	9/16" - 1-1/8"	1	1	0.160#	Ea
V45P	28525	7/16" Hex	5/8-18	1/4"	VPD4	1/2"	1-1/4" - 6"	1	1	0.500#	Ea

