


## Insulated Industrial Pliers & Cutters

Tools meet ASTM, IEC, VDE, EN, NFPA & CSA standards

10,000 Volt tested  
1000 Volt Rated

Industrial brushed finish



**NEW**  
From Wiha

 **1000V**

Induction hardened jaws and cutters to 60 HRC

Two component ergo cushion grip handles




**New dynamic joint provides 40% easier cuts & significantly longer tool life**


## Insulated Lineman's Pliers With Crimpers

**NEW**  
From Wiha



Long life high performance dynamic 60/40 joint

 **1000volt**

**WH32917 Insulated Industrial Lineman's Pliers "5-In-1" Professional Design** Insulation According to EN/IEC, ASTM, NFPA70E & CSA,  **up to 1000 volt. Individually Tested.** Deep cut radius conduit jaws for non-slip handling. Sure grip knurled & cross hatched flat jaw for non-slip gripping. Extra long induction hardened precision matched cutting edges. Lower crimping jaw accepts most standard non-insulated electrical connectors. Large head with square anvil surface on each side. Premium CV tool steel forgings.


Item	↔	↔	Cutting Capacity	☐	↕
No.	mm	Inch	Copper AWG	Pkg.	wt.
WH32917	225	9.0	#4	1	.98

## Insulated Long Nose Pliers With Cutters

**NEW**  
From Wiha



 **1000volt**

**WH329 Insulated Industrial Long Nose Pliers With Cutters.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  **up to 1000 volt. Individually Tested.** Drop-forged from special tool steel, cutters additionally induction hardened (approx. 60 HRC), half-round jaws, serrated gripping surface. Industrial brushed finish. Ergonomic comfort grip with slip guard.

Item	↔	↔	Cutting Capacity	☐	↕
No.	mm	Inch	Copper AWG	Pkg.	wt.
WH32926	160	6.3	#10	1	.36
WH32923	200	8.0	#8	1	.46


## Insulated Diagonal Cutters

**NEW**  
From Wiha



Long life high performance dynamic 60/40 joint

 **1000volt**

**WH329 Insulated Industrial Diagonal Cutters.** Insulation According to VDE 0682/part 201, EN/IEC 60900, ASTM F-1505-01, NFPA70E & CSA,  **up to 1000 volt. Individually Tested.** DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long term cutting is achieved through additional inductive hardening to approx. 60 HRC. Special tool steel hardened and tempered. Industrial brushed finish. For soft, medium hard wire & piano wire.

Item	↔	↔	Cutting Capacity	☐	↕
No.	mm	Inch	Copper AWG	Pkg.	wt.
WH32933	160	6.3	#6	1	.64
WH32929	200	8.0	#6	1	.80