

C-CP-A-SQ-79L Series

LED Canopy Light - Wide Distribution - Medium
Replaces 200W MH

C-LITE
LED LIGHTING BY CREE



BIGGER, BRIGHTER & MORE EFFICIENT! USE FEWER FIXTURES & GET GREAT RESULTS!

EFFICIENT

- Delivers up to 44% more light than comparable HID fixtures
- Uses 1/3 of the energy of comparable HID fixtures

LONG-LASTING

- Polyester powder-coat finish for long-lasting color
- Designed to last over 172,000 hours

RECOMMENDED USE

- Security
- Entryways
- Perimeter Lighting
- Exterior canopies

INPUT VOLTAGE

- Universal (120V through 277V Operation)


CERTIFICATIONS:



US: c-lite.com

T (800) 236-6800 F (262) 504-5415

C-CP-A-SQ-79L Series



Series overview

DIMENSIONS	PRODUCT WEIGHT	MOUNTING HEIGHT	SPACING
10-7/8" L x 10-7/8" W x 5-1/2" H 13-1/3" L x 13-1/3" W (Outer Edge)	8.54 lbs.	10 to 20 feet	4 times the mounting height


Fixture Specifications

HOUSING	Low-copper, die-cast aluminum housing Dark bronze or white polyester powder-coat finish
LENS ASSEMBLY	UV-stabilized acrylic prismatic refractor with self-retaining screws
MOUNTING	3/4" conduit entry on top for pendant mounting 1/2" conduit entries on two sides

Electrical Performance

OPERATING MINIMUM	LIFESPAN <small>L₇₀ AT 25°C (77°F)</small>	POWER FACTOR	TOTAL HARMONIC DISTORTION	DIMMABLE
-40°C (-40°F)	Estimated 172,000 Hours	> 0.9	< 20%	No
INPUT VOLTAGE	120V	208V	240V	277V
CURRENT DRAW (Amps)	0.80A	0.50A	0.40A	0.35A

CORRELATED COLOR TEMPERATURE (CCT)



Warranty and Certifications

Warranty	UL Listed	Energy Star
5-Year Limited*	Wet Locations	N/A

C-CP-A-SQ-79L Series

Output Specifications

SKU	Light Output	Color Temp (see chart)	Power Consumption	Color Accuracy	Replaces
C-CP-A-SQ-79L-50K-DB	7,900 Lumens	Cool White (5000K)	67W	≥ 70 CRI	200W MH
C-CP-A-SQ-79L-40K-DB	7,900 Lumens	Neutral White (4000K)	67W	≥ 70 CRI	200W MH
C-CP-A-SQ-79L-50K-WH	7,900 Lumens	Cool White (5000K)	67W	≥ 70 CRI	200W MH
C-CP-A-SQ-79L-40K-WH	7,900 Lumens	Neutral White (4000K)	67W	≥ 70 CRI	200W MH

Photometric Diagram



All published photometric testing performed to IESNA LM-79-08 standards by a NVLAP certified laboratory. Fixture photometry was completed on a single representative fixture.