

## SELECTION CHARTS

Three Phase

### GROUP A



#### 208 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS — 3Ø, 60 Hz

KVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS	WEATHER SHIELD P/N	Electrical Connections and Design Figures Begin on Page 54
		HEIGHT	WIDTH	DEPTH					
15.0	T-3-79367-1S	18.86 (48.0)	20.30 (51.6)	9.03 (22.9)	245 (111.0)	F ①	NA	NA	48-I
30.0	T-2-79368-4S	25.50 (64.8)	24.40 (62.0)	19.40 (49.3)	330 (150.0)	F ①	NA	WS-A-1	46-E
45.0	T-2-79369-4S	25.50 (64.8)	24.40 (62.0)	19.40 (49.3)	400 (181.0)	F ①	NA	WS-A-1	46-E
75.0	T-2-79370-4S	29.90 (76.0)	28.20 (71.6)	22.40 (56.9)	530 (240.0)	F ①	NA	WS-A-2	46-E
112.5	T-2-79371-4S	35.90 (91.2)	31.90 (81.0)	26.90 (68.3)	750 (340.0)	F	NA	WS-A-3	46-E
150.0	T-2-79372-4S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	950 (430.9)	F	NA	WS-A-4	46-E
225.0	T-2-79373-4S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1200 (544.0)	F	NA	WS-A-4	46-E
300.0	T-3-79374-4S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	NA	WS-A-5	46-E
500.0	T-2-79376-2S	57.80 (146.8)	45.00 (114.3)	41.50 (105.4)	3500 (1588.0)	F	NA	WS-A-6	② G

### GROUP B

#### 240 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

KVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Electrical Connections and Design Figures Begin on Page 54
		HEIGHT	WIDTH	DEPTH					
9.0	T-2A-53360-1S	14.03 (36.0)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	18-F
15.0	T-3-53361-1S	18.86 (48.0)	20.30 (51.6)	9.03 (23.0)	250 (113.0)	F ①	NA	NA	18-I
30.0	T-3-53362-4S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	325 (147.0)	F ①	NA	WS-A-1	19-E
45.0	T-3-53363-4S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	350 (158.8)	F ①	NA	WS-A-1	19-E
75.0	T-3-53364-4S	29.90 (75.9)	28.15 (71.5)	22.37 (56.8)	450 (204.1)	F ①	NA	WS-A-2	19-E
112.5	T-2A-53365-4S	35.90 (91.2)	31.90 (81.0)	26.88 (68.3)	696 (294.8)	F	NA	WS-A-3	19-E
150.0	T-2-53366-4S	41.52 (105.5)	32.90 (84.0)	29.88 (75.9)	978 (412.8)	F	NA	WS-A-4	19-E
225.0	T-2-53367-4S	41.52 (105.5)	32.90 (84.0)	29.88 (75.9)	1200 (544.0)	F	NA	WS-A-4	19-E

### GROUP C

#### 416 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

KVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Electrical Connections and Design Figures Begin on Page 54
		HEIGHT	WIDTH	DEPTH					
3.0	T-2A-79340-2S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	NA	66-F
6.0	T-2A-79341-2S	11.38 (28.9)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	NA	66-F
9.0	T-2A-79342-2S	14.03 (35.6)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	66-F
15.0	T-3-79343-4S	18.86 (48.0)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	NA	47-I
30.0	T-2A-79344-4S	25.48 (64.8)	24.39 (62.0)	19.37 (49.3)	325 (147.0)	F ①	NA	WS-A-1	47-E
45.0	T-2A-79345-4S	25.50 (64.8)	24.40 (62.0)	19.40 (49.3)	400 (181.0)	F ①	NA	WS-A-1	47-E
75.0	T-3-79346-4S	29.90 (76.0)	28.15 (71.5)	22.40 (56.9)	600 (272.0)	F ①	NA	WS-A-2	47-E
112.5	T-2A-79347-4S	35.90 (91.2)	31.90 (81.0)	26.88 (68.3)	750 (340.0)	F	NA	WS-A-3	47-E
150.0	T-2-79348-4S	41.52 (105.5)	32.90 (83.6)	29.88 (75.9)	1125 (510.0)	F	NA	WS-A-4	47-E
225.0	T-2-79349-4S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1500 (544.0)	F	NA	WS-A-5	47-E
300.0	T-3-79350-4S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	NA	WS-A-5	47-E
500.0	T-1-79351-4S	62.00 (157.5)	54.00 (137.2)	42.00 (106.7)	2675 (1213.0)	F	NA	WS-B-3	② G

① Wall mounting brackets are available for these sizes, refer to page 64.

② Consult factory for wiring diagram.