

THREE PHASE



480 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS
MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

KVA ②	GROUP A CATALOG NO. 80°C RISE	GROUP B CATALOG NO. 115°C RISE	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	WEATHER SHIELD P/N	Electrical Connections and Design Figures Begin on Page 42
			HEIGHT	WIDTH	DEPTH				
30.0	ME-2-53312-8S	ME-2-53312-1S	29.90 (75.9)	28.15 (71.5)	22.37 (56.8)	345 (157.0)	F ①	WS-A-1	22-E
45.0	ME-2-53313-8S	ME-2-53313-1S	29.90 (75.9)	28.15 (71.5)	22.37 (56.8)	425 (193.0)	F ①	WS-A-1	22-E
75.0	ME-2-53314-8S	ME-2-53314-1S	35.90 (91.2)	31.90 (81.0)	26.88 (68.3)	575 (261.0)	F	WS-A-3	22-E
112.5	ME-2-53315-8S	ME-2-53315-1S	41.52 (105.5)	32.90 (83.6)	29.88 (75.9)	970 (440.0)	F	WS-A-4	22-E
150.0	ME-2-53316-8S	ME-2-53316-1S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1140 (517.0)	F	WS-A-4	22-E
225.0	ME-2-53317-8S	ME-2-53317-1S	46.00 (116.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	WS-A-5	22-E
300.0	ME-1-53318-8S	ME-1-53318-1S	52.00 (132.1)	52.00 (132.1)	40.00 (101.6)	2225 (1009.0)	F	WS-A-60	23-G
500.0	ME-2-53319-8S	ME-2-53319-1S	62.80 (159.5)	54.00 (137.2)	49.50 (125.7)	3525 (1599.0)	F	WS-A-6	22-G

480 DELTA PRIMARY VOLTS — 240 DELTA SECONDARY VOLTS
MAY BE USED ON A 4 WIRE 480Y/277 VOLT SUPPLY — 3Ø, 60 Hz

KVA ②	GROUP C CATALOG NO. 80°C RISE	GROUP D CATALOG NO. 115°C RISE	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	WEATHER SHIELD P/N	Electrical Connections and Design Figures Begin on Page 42
			HEIGHT	WIDTH	DEPTH				
30.0	T-3-53342-8S	T-3-53342-1S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	400 (181.0)	F ①	WS-A-1	26-E
45.0	T-3-53343-8S	T-3-53343-1S	29.90 (75.9)	28.15 (71.5)	22.37 (56.8)	600 (272.0)	F ①	WS-A-2	26-E
75.0	T-2A-53344-8S	T-2A-53344-1S	35.90 (91.2)	31.90 (81.0)	26.88 (68.3)	750 (340.0)	F	WS-A-3	26-E
112.5	T-2-53345-8S	T-2-53345-1S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	910 (413.0)	F	WS-A-4	26-E
150.0	T-2-53346-8S	T-2-53346-1S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1110 (504.0)	F	WS-A-4	26-E
225.0	T-2-53347-8S	T-2-53347-1S	46.00 (116.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	WS-A-5	26-E
300.0	T-1-53348-8S	T-1-53348-1S	62.00 (157.5)	54.00 (137.2)	42.00 (106.7)	2675 (1213.0)	F	WS-A-57	27-G

NEW

600 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

KVA ②	GROUP E CATALOG NO. 80°C RISE	GROUP F CATALOG NO. 115°C RISE	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	WEATHER SHIELD P/N	Electrical Connections and Design Figures Begin on Page 42
			HEIGHT	WIDTH	DEPTH				
30.0	ME-2-13102-8S	ME-2-13102-1S	26.00 (66.0)	24.40 (62.0)	19.40 (49.3)	345 (157.0)	F ①	WS-A-1	29-E
45.0	ME-2-13103-8S	ME-2-13103-1S	29.40 (74.7)	28.20 (71.6)	22.40 (56.9)	425 (193.0)	F ①	WS-A-2	29-E
75.0	ME-2-13104-8S	ME-2-13104-1S	35.40 (89.9)	31.90 (81.0)	26.90 (68.3)	575 (261.0)	F	WS-A-3	29-E
112.5	ME-2-13105-8S	ME-2-13105-1S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	970 (440.0)	F	WS-A-4	29-E
150.0	ME-2-13106-8S	ME-2-13106-1S	41.50 (105.4)	32.90 (83.6)	29.90 (75.9)	1140 (517.0)	F	WS-A-4	29-E
225.0	ME-2-13107-8S	ME-2-13107-1S	45.60 (115.8)	39.50 (100.3)	35.50 (90.2)	1550 (703.0)	F	WS-A-5	29-E
300.0	ME-1-13099-8S	ME-1-13099-1S	52.00 (132.1)	52.00 (132.1)	40.00 (101.6)	2225 (1009.0)	F	WS-A-60	30-G
450.0	ME-1-13111-8S	ME-1-13111-1S	64.00 (162.6)	60.00 (152.4)	42.00 (106.7)	3500 (1588.0)	F	WS-B-4	30-G
500.0	ME-1-13112-8S	ME-1-13112-1S	64.00 (162.6)	60.00 (152.4)	42.00 (106.7)	3525 (1599.0)	F	WS-B-4	30-G

① Wall mounting brackets are available for these sizes, refer to page 50.
 ② 30 through 300 KVA provided with 120V Lighting Tap limited to 5% of Nameplate Rating.