

## TDGPX Series



### FEATURES & BENEFITS

- NEMA 5 flanged enclosure 1 kVA & greater
  - ◆ NEMA 12 less than 1 kVA
  - ◆ Receptacle 1 kVA & greater
- Lockable 30 Amp fuseable disconnect switch
- Power on Pilot Light
- UL listed Industrial Control Transformer
- 250 VA through 3000 VA
  - Available with Primary and Secondary Fusing
    - ◆ Class CC fusing on Primary
    - ◆ 13/32" x 1 1/2" fusing on Secondary
- 200,000 Amp Short Circuit protection
- UL & cUL Listed

### APPLICATIONS

- Automotive Industry
- Localized Power Driving Maintenance

TDGP DISCONNECT TRANSFORMERS  
480 PRIMARY VOLTS — 120 SECONDARY VOLTS — 1Ø, 60 Hz



VA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			NO. OF RECEPTACLES	POWER-ON INDICATOR LAMP	KNOCKOUTS Inches (Cm.)	APPROX. SHIP WEIGHT Lbs. (kg.)
		A	B	C				
250	TDGP0250XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	0	YES	N/A	38 (14.1)
500	TDGP0500XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	0	YES	N/A	43 (19.5)
750	TDGP0750XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	0	YES	N/A	51 (23.1)
1000	TDGP1000XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	2	YES	N/A	54 (24.5)
1500	TDGP1500XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	2	YES	N/A	66 (29.9)
2000	TDGP2000XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	2	YES	N/A	73 (33.1)
3000	TDGP3000XM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	2	YES	N/A	93 (42.2)
1000	TDGP1000SXM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	2	YES	N/A	54 (24.5)
3000	TDGP2000SXM	8.97 (22.8)	14.00 (35.6)	12.61 (32.0)	2	YES	N/A	93 (42.2)

## Design Figures & Wiring Diagrams

