



## Catalog No. THHQB1115GF

Description: THHQB 1115 CIRCUIT BREAKER

UPC No 783164123654

Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line

### Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

### Descriptors

Category	Q-Line Miniature Circuit Breakers
GO Schedule	B1

### Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	15 A
System Voltage	120 Vac, 120/240 Vac
Poles	1
Trip Function	LIG
Continuous Current Rated	Standard
120 Vac Interrupting Rating	22 KAIC
120/240 Vac Interrupting Rating	22 KAIC
Suitable for Reverse Feed	Yes
Product Line	TEY / Q-Line (Bolt-On)
Long Time	Fixed
Instantaneous	Fixed
Ground Fault	Yes
Protective Relays	No
Current Metering	No
GSA Compliance	No

### Classifications

UL File #	E51075
CSA File#	LR10263

## Publications

Title	Publication No.	Publication Type
<a href="#">Q-Line MCCB, 100A Frame 1- Pole with Ground Fault Protection, Drawing</a> 1-Page, Fully dimensioned outline drawing in .pdf format	139C4005-SH1	Drawings-Outline and Dimensional
<a href="#">Ground Fault Circuit Interrupter with Self-Test Feature (GFCI)</a> Rev A. 2 Pages. Installation, troubleshooting, and testing guide for type THQ/THHQ 15A-30A, 1 Pole circuit breakers.	GEH-4338	Installation and Instruction
<a href="#">15A-20A, 1 Pole</a> Installation Instructions	GEH-41543	Installation and Instruction

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.