

» SBE Series Industrial Control Transformers

Epoxy encapsulated for protection against dust, mildew, and other contaminants



Features

- 50/60 Hz models available
- Copper windings
- Standard power ratings from 50 through 1000VA
- 55° C rise, 105° C insulation system
- Meet or exceed NEMA Standard ST 1 and ANSI C89.1
- Integrally molded, flame-retardant (IEC 60707 ISO Class 1210) terminal blocks



Mfr.'s Model No.	VA	Dimensions (H x W x D) (in.)	Approx. Ship Weight (lbs.)	Price
120 x 240V Primary; 24V Secondary; 60 Hz				
E050E	50	2.72"H x 3.01"W x 3.99"D	3	\$49.06
E075E	75	2.96"H x 3.39"W x 4.36"D	4	\$61.66
E100E	100	2.96"H x 3.39"W x 4.61"D	5	\$65.87
E150E	150	3.89"H x 4.5"W x 4.48"D	8	\$79.88
E200E	200	3.89"H x 4.5"W x 4.79"D	10	\$103.72
E250E	250	3.89"H x 4.5"W x 5.21"D	11	\$113.53
E300E	300	4.53"H x 5.25"W x 4.66"D	12	\$121.95
E350E	350	4.53"H x 5.25"W x 5.07"D	15	\$138.76
E500E	500	4.53"H x 5.25"W x 5.75"D	19	\$159.77
E750E	750	5.56"H x 6.38"W x 6.93"D	31	\$201.81
220 x 440V Primary; 110V Secondary, 50/60 Hz / 230 x 460V Primary; 115V Secondary; 50/60 Hz / 240 x 480V Primary, 120V Secondary; 60 Hz				
E050	50	2.72"H x 3.01"W x 3.99"D	3	\$43.45
E075	75	2.96"H x 3.39"W x 4.36"D	4	\$49.06
E100	100	2.96"H x 3.39"W x 4.61"D	5	\$53.27
E150	150	3.89"H x 4.5"W x 4.48"D	8	\$63.08
E200	200	3.89"H x 4.5"W x 4.79"D	10	\$75.69

*CE - IEC 61558-1, IEC 61558-2-2.

Mfr.'s Model No.	VA	Dimensions (H x W x D) (in.)	Approx. Ship Weight (lbs.)	Price
220 x 440V Primary; 110V Secondary, 50/60 Hz / 230 x 460V Primary; 115V Secondary; 50/60 Hz / 240 x 480V Primary, 120V Secondary; 60 Hz (cont.)				
E250	250	3.89"H x 4.5"W x 5.21"D	11	\$89.70
E300	300	4.53"H x 5.25"W x 4.66"D	12	\$93.91
E350	350	4.53"H x 5.25"W x 5.07"D	15	\$105.12
E500	500	4.53"H x 5.25"W x 5.75"D	19	\$126.13
E750	750	5.56"H x 6.38"W x 6.93"D	31	\$173.79
E1000	1000	5.56"H x 6.38"W x 7.36"D	36	\$225.65
International Series Control Transformers — 208/240/415V Primary; 24V Secondary; 50/60 Hz / 277/480V Primary; 24V Secondary; 60 Hz / 200/230/400V Primary; 24V Secondary; 50/60 Hz / 220/380V Primary; 23V Secondary; 50/60 Hz, CE Marked*				
E050TE	50	2.96"H x 3.39"W x 4.36"D	4	\$176.59
E100TE	100	3.89"H x 4.5"W x 4.48"D	8	\$179.39
E150TE	150	3.89"H x 4.5"W x 5.21"D	11	\$183.61
E250TE	250	4.53"H x 5.25"W x 5.53"D	15	\$232.66
E500TE	500	5.56"H x 6.38"W x 6.93"D	30	\$334.96

Power Supply & Protection

» SCP-X Extreme Environment Series

Rugged power supply designed for use in extreme environments

Features

- IP66/67 versatile/NEMA 4X rated
- 24 VDC, 115/230 VAC, 3.8A nominal current
- Listed power supply for standalone applications
- High ambient temperature up to 60° C without derating
- DC OK Green LED
- Worldwide approvals
- Five-year warranty



Mfr.'s Model No.	Description	Price
SCP100S24XCP	100W, 24V, External Environmental Controls, DCPS	\$426.82
SCP100S24XDVN	100W, 24V, External Environmental Controls, DCPS DEVNET	\$426.82

» SDN-C Series Compact DIN Rail Power Supplies

SDN-C Series DIN rail power supplies are the next generation of the SDN Series. These models combine high efficiency and compact size with visual diagnostic LEDs. Features include sag immunity, power factor correction, and universal voltage input. Wide temperature operating range and parallel operation capability make the SDN-C units suitable to a variety of industrial applications.

Features

- Visual diagnostic LEDs for input/output status
- Higher efficiency saves energy, lowers heat generation
- Powerboost™ overload capability to start high inrush loads
- Accepts universal voltage 85–264 VAC, 50/60 Hz input
- Meets SEMI F47 Sag Immunity
- Power factor correction meets EN61000-3-2
- Class 1, Div. 2 hazardous locations rating; ATEX approval on select models*
- DIN rail mounting clip
- User-adjustable output voltage accessible via front face
- Parallel capability standard
- -25° to 60° C operation without derating
- LEDs for status; large, rugged, accessible screw terminals; easy ON/OFF DIN mounting
- High MTBF



Mfr.'s Model No.	Output Voltage	Output Current	Input Current	Input Voltage	Dimensions	Price
SDN 5-24-100C*	23.5–28.5 VDC	5A	1.65–0.55A	85–264 VAC	4.88"H x 1.94"W x 4.36"D	\$351.57
SDN 10-24-100C*	23.5–28.5 VDC	10A	3.2–1A	85–264 VAC	4.88"H x 2.37"W x 4.36"D	\$511.98
SDN 20-24-100C	23.5–28.5 VDC	20A	6/3A	85–264 VAC	4.88"H x 3.42"W x 4.98"D	\$773.97