

ENCLOSED ELECTRONIC 24V

Transformers

WAC LIGHTING

Responsible Lighting®

Fixture Type:

Catalog Number:

Project:

Location:



PRODUCT DESCRIPTION

Combining Class 2 Transformers in a single package creates a single source to wire multiple runs of low voltage fixtures such as under cabinet and display luminaires.

FEATURES

- 1W minimum load
- Secondary wiring for Class 2 transformers does not require conduit sheathed cable or clamp wiring techniques
- Intrinsically safe, Class 2 transformers permit no greater than a 5 amp current be drawn
- Non-metallic sheathed cable may be used for secondary wiring in walls and ceilings
- Drop down to a smaller gauge wire if space in fixture does not permit secure connection directly with the non-metallic sheathed cable
- Powers most cabinet fixtures

SPECIFICATIONS

Construction: Built-in auto reset, soft start, short and overload circuit protection features. The soft start delayed start feature extends lamp life by delaying the abrupt inrush current to the lamp.

Output: 24V

Frequency: 20khz

Dimming: Dimmable with electronic low voltage dimmers. Dimmers should always be installed on the primary side of the transformer.

Details: Enclosure has knockouts on three sides. Screw holes are located on one long side for securing enclosure in place.

Standards: UL Listed

ORDER NUMBER

Model	Input	Output	Min Load	L x W x H	Class 2	Auto Reset	LED Indicator and push in terminals
EN-2460-RB2	120VAC	24VAC 60W	1W	6 1/2" x 1 5/8" x 1 1/4"	Yes	No	No
EN-24100-RB2	120VAC	24VAC 100W	1W	6 1/2" x 1 5/8" x 1 1/4"	Yes	No	No
EN-24150-RB-AR	120VAC	24VAC 150W	1W	6 1/4" x 3" x 1 5/8"	No	Yes	No
EN-B24PZ-AR	120VAC	24VAC 300W	1W	6 1/4" x 3 3/8" x 2 1/8"	no	Yes	No

EN- _ _ - _ -

Example: **EN-12100-RB-AR**

wacighting.com

Phone (800) 526.2588

Fax (800) 526.2585

Headquarters/Eastern Distribution Center

44 Harbor Park Drive

Port Washington, NY 11050

Central Distribution Center

1600 Distribution Ct

Lithia Springs, GA 30122

Western Distribution Center

1750 Archibald Avenue

Ontario, CA 91760